

## FM-SR086CUTN-ST-BULK DATA SHEET

# RG405 Type .086 Semi-Rigid Coax Cable with a Tin Plated Copper Outer Conductor in Straight Sections

.086 diamater semi-rigid coaxial cable is the cable of choice for many RF and Microwave engineers. 0.086 cables sometimes referred to as RG405 based on the mil specification for semi-rigid cable of this diameter has a maximum operating frequency of 40 GHz. This form factor is widely used in the RF industry and many connector series and configurations are available for this cable. Because of the solid copper wall design the cable can be formed using proper tooling with a minimum inside bend radius of .05 inches.

## **Electrical Specifications**

Description	Min	Т	ур	Max	Units	
Frequency Range	DC			40	GHz	
Impedance		ī	50		Ohms	
DWV (AC)				5,000	Vrms	

#### **Performance by Frequency Band**

Description	F1	F2	F3	F4	F5	Units
Frequency	1	10	20			GHz
Attenuation, Typ	22 72.18	80 262.47	120 393.7			dB/100ft dB/100m
Power In (CW), Max	130	35	20			Watts
Power In (CW), Max	130	35	20			

#### **Mechanical Specifications**

Min. Bend Radius (Installation)

0.05 in [1.27 mm]

## **Construction Specifications**

Description	<b>Material and Plating</b>	Diameter
Inner Conductor	Copper Clad Steel, Silver	0.02 in [0.51 mm]
Conductor Type	Solid	
Dielectric	PTFE	0.066 in [1.68 mm]
Outer Conductor	Copper, Tin	0 in [0 mm]

## **Environmental Specifications**

Temperature

Operating Range -55 to +125 deg C

**Compliance Certifications** (see product page for current document)

## **Plotted and Other Data**

Notes:

## **Configuration:**

- Semi-Rigid Cable
- 0 Shield(s)

#### Features:

- Silver Plated Copper Clad Steel center conductor
- PTFE dielectric material
- Copper Tinned Outer Conductor
- Operating to 40 GHz
- Minimum inside bend radius of .05 inches
- ROHS compliant

## **Applications:**

- RF and Microwave Cable Assemblies to 40 GHz
- Preformed cable assemblies to insure fit and layout
- Test Equipment port jumpers

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





RG405 Type .086 Semi-Rigid Coax Cable with a Tin Plated Copper Outer Conductor in Straight Sections from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: RG405 Type .086 Semi-Rigid Coax Cable with a Tin Plated Copper Outer Conductor in Straight Sections FM-SR086CUTN-ST-BULK

The information contained in this document is accurate to the best of our knowledge and representative of the part

URL: https://www.fairviewmicrowave.com/rg405-type-.086-semi-rigid-coax-cable-tin-plated-copper-fm-sr086cutn-st-bulk-p.aspx

described h	erein. It n	nay be n	ecessar	y to ma	ke modific	ations to t	he part a	nd/or t	he docun	nentation	of the part	t, in order
to implement	nt improve	ments. I	Fairview	Microw	ave reserv	es the rigl	nt to mak	e such	changes	as require	d. Unless	otherwise
stated, all s	specification	ns are n	ominal.	Fairvie	w Microwa	ve does n	ot make	any rep	resentat	on or wa	rranty rega	arding the
suitability o	f the part	describe	d hereir	for any	y particula	r purpose,	and Fair	view Mi	crowave	does not	assume ar	ny liability
arising out	of the use	of any pa	art or do	cument	ation.							



# FM-SR086CUTN-ST-BULK DATA SHEET

