

FM510M1043 DATA SHEET

10 dBi Omni Antenna 1,710-2,700 MHz N Type Connector

The LTE outdoor omnidirectional FM510M1043 antenna from Fairview Microwave is a high performance RF component which operates from 1710 to 2700 MHz. The FM510M1043 antenna is ideal for 5G, LTE, CDMA, LPWAN/IoT/M2M applications including LoRA, LTE-M, and NB-IOT. The Multi-Band design of the Fairview Microwave FM510M1043 antenna can be used for a wide array of cellular telecommunication wireless applications where wide coverage is desired. Fairview Microwaves FM510M1043 can be used to distribute Cellular signals throughout an outdoor area.

The Type N connectorized FM510M1043 antenna with vertical polarization from Fairview Microwave provides excellent outdoor coverage for all base station applications. The Type N connectorized FM510M1043 antenna from Fairview Microwave excels in large open areas. The mounting bracket and hardware are included for easy installation. Fairview Microwave LTE outdoor omnidirectional with Type N female purchases will ship the same day. Our FM510M1043 antenna is part of over one million RF, microwave and millimeter wave components in stock and ready for same-day shipment worldwide.



- All weather operation
- Includes heavy duty steel mast mounting brackets
- Lightweight fiberglass radome
- Integral N-Female connector
- Rugged industrial grade design
- 360° Omnidirectional Pattern
- 10 dBi gain

Configuration

Design Polarization Connector Type Number of Ports Omni Vertical N Female

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	1,710		2,700	MHz
Impedance		50		Ohms
Gain		10		dBi
Input Power			50	Watts
VSWR			2.3:1	

Applications:

- 1800, 1900, 2100, 2600 Cellular Band Operation
- Supports midband LTE and 5G networks
- Point to Multipoint and Non Line of Sight (NLOS) Applications

Mechanical Specifications

Radome Material Fiberglass

Size

 Length
 38.6 in [980.44 mm]

 Width
 1.6 in [40.64 mm]

Maunting Mast Diameter 1.18 to 2.36 in [29.97 to 59.94

mm]

Weight 5.07 lbs [2.3 kg]

Environmental Specifications Temperature

Operating Range -40 to +70 deg C

Wind Loading 124.27 MPH [199.99 KPH]

Humidity

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

sales@fairviewmicrowave.com

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com





Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

10 dBi Omni Antenna 1,710-2,700 MHz N Type Connector from Fairview Microwave is in-stock and available to ship sameday. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 10 dBi Omni Antenna 1,710-2,700 MHz N Type Connector FM51OM1043

URL: https://www.fairviewmicrowave.com/antenna-10-dbi-n-female-fm51om1043-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





