

# Miter RA N Female to TNC Female Adapter with Passivated Stainless Steel Body, DC to 18 GHz

Miter RA type N female to TNC female adapter part number FMAD1580 from Fairview Microwave is in-stock and ships same day. This Fairview type N to TNC adapter has a female to female gender configuration and is built of durable stainless steel. FMAD1580 type N female to TNC female adapter operates to 18 GHz. The Fairview Microwave RF adapter provides good VSWR of 1.35:1 maximum. This miter right angle type N to TNC adapter allows for easier connections in tight spaces.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

### **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	DC		18	GHz
VSWR			1.35:1	

## **Mechanical Specifications**

cinamear opecimeatin	0115	
<b>Size</b> Length Width Height		1.300 in [33.0 mm] 0.63 in [16 mm] 1.28 in [32.51 mm]
Weight		0.023 lbs [10.43 g]
Description	Connector 1	Connector 2
Туре	N Female	TNC Female
Polarity	Standard	Standard
Mating Cycles	500	500

#### **Material Specifications**

Description	Connector 1	Connector 2	
Туре	N Female	TNC Female	
Contact Material	Beryllium Copper	Beryllium Copper	
Contact Plating	Gold over Nickel	Gold over Nickel	
Insulation Material	Oxide-Noryl	Oxide-Noryl	
Outer Contact Material	Passivated Stainless Steel	Passivated Stainless Steel	
Body Material	Passivated Stainless Steel	Passivated Stainless Steel	



**DATA SHEET** 

**FMAD1580** 



# **Configuration:**

- N Female Connector 1
- TNC Female Connector 2
- 50 Ohm
- Miter Right Angle Body Geometry

## **Features:**

- VSWR of 1.35:1 max up to 18 GHz
- Gold over Nickel Plated
  Beryllium Copper Contact

# **Applications:**

- Enables Between Series
  Connections
- General Purpose Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





#### **Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**


Notes:

Miter RA N Female to TNC Female Adapter with Passivated Stainless Steel Body, DC to 18 GHz from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Miter RA N Female to TNC Female Adapter with Passivated Stainless Steel Body, DC to 18 GHz FMAD1580

URL: https://www.fairviewmicrowave.com/n-jack-tnc-jack-right-angle-adapter-fmad1580-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



Fairview Microwave



## an INFINIT<sup>©</sup> brand



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689