

High Temperature Adapter 4 Hole Flange 2.4mm Female to 2.4mm Female, 50GHz VSWR1.3, MIL-STD 348B with Stainless Steel Body

4 hole flange 2.4mm female to 2.4mm female adapter part number FMAD1645 from Fairview Microwave is in-stock and ships same day. This Fairview 2.4mm to 2.4mm adapter has a female to female gender configuration and is built of stainless steel in a high temperature adapter design. FMAD1645 2.4mm female to 2.4mm female adapter operates to 50 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.3:1 maximum. The 2.4mm connector mates mechanically with commercially available 1.85mm (V) connectors. Our RF 2.4mm 4 hole flange to 2.4mm adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.


Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		50	GHz
VSWR			1.3:1	
Insertion Loss			0.29	dB
Operating Voltage (AC)			100	Vrms
DWV (AC)			500	Vrms
Insulation Resistance	5,000			MOhms
RF Leakage			100	dB

Mechanical Specifications

Size	
Length	0.73 in [18.54 mm]
Width	0.50 in [12.70 mm]
Height	0.50 in [12.70 mm]
Weight	0.01 lbs [5.90 g]

Description	Connector 1	Connector 2
Type	2.4mm Female	2.4mm Female
Polarity	Standard	Standard
Mating Cycles, Min	500	500
Mating Torque	7.08 to 9.74 in-lbs [0.80 to 1.10 Nm]	7.08 to 9.74 in-lbs [0.80 to 1.10 Nm]
Contact Retention Force, Min	60.7 lbs [27.53 kg]	60.7 lbs [27.53 kg]
Contact Captivation Axial Force, Min	4.5 lbs [2.04 kg]	4.5 lbs [2.04 kg]
Coupling Proof Torque	15 in-lbs [1.7 Nm]	15 in-lbs [1.7 Nm]



Configuration:

- 2.4mm Female Connector 1
- 2.4mm Female Connector 2
- 50 Ohm
- High Temperature Adapter Design
- Straight Body Geometry
- 4 Hole Flange Mount Method

Features:

- VSWR of 1.3:1 max up to 50 GHz
- Gold over Nickel Plated Beryllium Copper Contact

Applications:

- General Purpose Test
- Rack Mounted Equipment

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Material Specifications

Description	Connector 1	Connector 2
Type	2.4mm Female	2.4mm Female
Contact Material	Beryllium Copper	Beryllium Copper
Contact Plating	Gold over Nickel	Gold over Nickel
Insulation Material	PEI	PEI
Body Material	Stainless Steel	Stainless Steel
Body Plating	Passivated	Passivated

Environmental Specifications

Temperature

Operating Range

Humidity

Thermal Shock

Salt Spray

-50 to +170 deg C

MIL-STD-202, Method 206

MIL-STD-202, Method 107, Condition B

MIL-STD-202, Method 101, Condition B

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

High Temperature Adapter 4 Hole Flange 2.4mm Female to 2.4mm Female, 50GHz VSWR1.3, MIL-STD 348B with Stainless Steel Body from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [High Temperature Adapter 4 Hole Flange 2.4mm Female to 2.4mm Female, 50GHz VSWR1.3, MIL-STD 348B with Stainless Steel Body FMAD1645](#)

URL: <https://www.fairviewmicrowave.com/high-temperature-adapter-4-hole-flange-2.4mm-female-to-2.4mm-female-adapter-mil-std-202-method-206-50ghz-vswr1.3-mil-std-348b-with-stainless-steel-body-fmad1645-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

