



Slide-On BMA Jack 2 Hole Flange to SMP Female Cable RG405 Type .086 Coax

The BMA jack slide-on 2 hole flange to SMP female cable using RG405 type .086 coax, part number FMCA1607, from Fairview Microwave is in-stock and ships same day. This Fairview BMA to SMP cable assembly has a jack to female gender configuration with 50 ohm semi-rigid FM-SR086CU coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA1607 BMA jack to SMP female cable assembly operates to 18 GHz. Our RF cable assembly with BMA 2 hole flange interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	Units
Frequency Range	DC			18	GHz
VSWR				1.5:1	
Return Loss				15.56	dB

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	4.5	9	18	GHz
Insertion Loss (Typ.)	0.22	0.28	0.46	0.74	1.13	dB/ft
	0.72	0.92	1.51	2.43	3.71	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Diameter 0.75 in [19.05 mm]

Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields
Outer Conductor Material and Plating

50 Ohms Solid Copper Clad Steel, Silver PTFE 1 Copper

FM-SR086CU

Repeated Minimum Bend Radius 0.05 in [1.27 mm]



Configuration:

- Slide-On BMA Jack 2 Hole Flange
- SMP Female
- FM-SR086CU

Features:

• Max Frequency 18 GHz

Applications:

- General Purpose
- Laboratory Use
- Rack and Panel
- BMA Cable RF Backplanes
- Phased Array Interconnects
- High Speed Switching Networks
- Blind Mate BMA Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Connectors

Description	Connector 1	Connector 2			
Туре	BMA Jack	SMP Female			
Mount Method	2 Hole Flange				
Specification		MIL-STD-348			
Impedance	50 Ohms	50 Ohms			
Connection Method	Slide-On				
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold			
Contact Plating Spec.	51.18µ in. minimum	MIL-G-45204			
Dielectric Type	PTFE	PTFE			
Outer Cond Material & Plating Beryllium Copper, Go					
Body Material & Plating	Stainless Steel, Gold	Beryllium Copper, Gold			
Body Plating Spec.	19.68µ in. minimum	MIL-G-45204			

Mechanical Specification Notes:

Environmental Specifications

Temperature

Operating Range

-55 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data


Notes:

^{*}All cable assemblies have a length tolerance of 1.5% or \pm 3/8", whichever is greater.





Typical Performance Data



How to Order

Example: FMCA1607-12 = 12 inches long cable

FMCA1607-100cm = 100 cm long cable





Slide-On BMA Jack 2 Hole Flange to SMP Female Cable RG405 Type .086 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: Slide-On BMA Jack 2 Hole Flange to SMP Female Cable RG405 Type .086 Coax FMCA1607

URL: https://www.fairviewmicrowave.com/bma-jack-smp-female-cable-rg405-type-.086-coax-fmca1607-p.aspx









STANDARD TOLERANCES
.X ±0.2
.X ±0.01

XX ±0.01 XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL, 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME, 3. DIMENSIONS ARE IN INCHES [mm].						
Slide-On BMA Jack 2 Hole Flange to SMP Female Cab RG405 Type .086 Coax	DWG NO FMCA16	CAGE CODE 3FKR5					
NOTOS TYPE 1000 COUX	CAD FILE 12/20/17	SHEET	SCAL	LE N/A SIZ	ZE A	CN2245	