

**902 to 928 MHz, RFID Flat Panel Antenna, 12 dBi
Gain RP SMA Male, PVC Radome, RHCP**

Fairview Microwave's FMANFP1062 is a RHCP RFID flat panel antenna. The FMANFP1062 with a 12 dBi gain nominal is a Directional antenna. Our 902 to 928 MHz antenna has Reverse Polarity SMA Male connector.

With an impedance of 50 Ohms and max input power of 20 Watts, the FMANFP1062 flat panel RHCP antenna is well suited for Radio Frequency Identification tag reading applications. This 902-928 MHz 12 dBi gain RFID antenna is highly directional providing the reader radio the capabilities of simultaneously reading a multitude of RFID tags with a high degree of accuracy.

Fairview Microwave's RFID FMANFP1062 has a radome made of PVC in White color and comes from a facility certified to ISO 9001:2015. This RP SMA Male connectized Antenna has an overall length of 36 in, width of 6 in, and weighs 4.85 lbs. Use our on-line ordering system to purchase your FMANFP1062 RFID Directional RHCP antenna 24 hours a day with same-day shipping and no MOQs (minimum order quantities).

Configuration

Design	Flat Panel
Gain	12
Polarization	RHCP
Cable Type	RG142
Connector Type	SMA Male Reverse Polarity
Lightning Protection	DC Grounded

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	902		928	MHz
Input VSWR			1.3:1	
Impedance		50		Ohms
Gain		12		dBi
Front to Back Ratio		20		dB
Horizontal (Azimuth) Beam Width		80		Degrees
Vertical (Elevation) Beam Width		18		Degrees
Input Power			20	Watts

Mechanical Specifications

Radome Material	PVC
Size	
Length	36 in [914.4 mm]
Width	6 in [152.4 mm]
Height	1 in [25.4 mm]
Weight	4.85 lbs [2.2 kg]
Connector 1	
Inner Conductor Material and Plating	Beryllium Copper, Gold
Inner Conductor Plating Specification	QQ-C-530
Coupling Nut Plating Specification	QQ-B-626
Body Material and Plating	Brass, Nickel
Body Plating Specification	QQ-B-626


Features:

- High Performance Multi-tag read/write Capabilities
- Concealable Design
- Right Hand Circular Polarized
- 902 to 928 MHz Frequency Range
- 2 Meter Cable
- RP SMA Male Connector

Applications:

- Radio Frequency Identification
- Inventory Management
- Access Control
- Data Collection
- Asset Tracking
- Livestock Management

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Environmental Specifications

Temperature

Operating Range -40 to +60 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

902 to 928 MHz, RFID Flat Panel Antenna, 12 dBi Gain RP SMA Male, PVC Radome, RHCP from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [902 to 928 MHz, RFID Flat Panel Antenna, 12 dBi Gain RP SMA Male, PVC Radome, RHCP FMANFP1062](#)

URL: <https://www.fairviewmicrowave.com/12-dbi-flat-panel-antenna-902-928-mhz-sma-connector-fmanfp1062-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

