

FMBT1630 DATA SHEET

10 MHz to 12 GHz SMA Broadband Bias Tee, Male Input, Rated to 2.5 Amps and 100 Volts, DC SMA Connector

The FMBT1630 is a Broadband Bias Tee that operates from 10 MHz to 12 GHz. This general purpose Bias Tee is used in applications that requrie a source of DC voltage and current to be injected into an RF circuit without affecting the RF signal through the main transmission path. The module is designed for a 50 ohm input/output impedance and displays impressive typical performance that includes 2 dB insertion loss, 40 dB Isolation, and 1.6:1 VSWR. The Bias Tee is rated for 2.5 Amps and +100 Volts max DC voltage. Maximum RF input power handling is 5W. The compact package uses an SMA Male connector at the RF input and an SMA Female connector at the RF output . A Female SMA connector is used for the DC port. Operational Temperature is -55° C to $+105^{\circ}$ C.

Electrical Specifications

Min	Тур	Max	Units
0.01		12	GHz
	50		Ohms
	1.6:1	2.1:1	
	2	3	dB
	40		dB
		100	Vdc
		2.5	Α
		5	Watts
	0.04	0.05	Ohm
0.005		15	GHz
	0.01	0.01 50 1.6:1 2 40 0.04	0.01 12 50 1.6:1 2.1:1 2 3 40 100 2.5 5 0.04 0.05

Electrical Specification Notes: Values at +25°C, sea level.

Mechanical Specifications

Size

 Length
 1.29 in [32.77 mm]

 Width
 0.85 in [21.59 mm]

 Height
 0.55 in [13.97 mm]

 Weight
 0.11 lbs [49.9 g]

Environmental Specifications

Temperature

Operating Range -55 to +105 deg C Storage Range -60 to +90 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



Configuration:

- RF Port Connector: SMA Male
 DC/RF Port Connector: SMA Female
- DC Port Connector: SMA Female

Features:

- General Purpose Broadband Bias Tee
- 10 MHz to 12 GHz Frequency Range
- Insertion Loss: 2 dB Typ
- Isolation: 40 dB typ
- VSWR: 1.6:1 typ
- RF Input Power Handling 5W max
- 50 Ohms Input and Output Matched
- SMA Male RF Input Connector
- SMA Female RF Output Connector
- DC Connector: SMA Female
- Operational Temperature: -55°C to +105°C
- Rating: 2.5A max DC Current and +100V max DC Voltage

Applications:


- Biasing for Antenna Amplifiers, Laser Diodes, Photo Diodes, Optical Modulators
- Test & Measurement
- SATCOM
- Wireless Communications Systems
- Power over Ethernet
- Base Stations and Radios

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Typical Performance Data









10 MHz to 12 GHz SMA Broadband Bias Tee, Male Input, Rated to 2.5 Amps and 100 Volts, DC SMA Connector from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 10 MHz to 12 GHz SMA Broadband Bias Tee, Male Input, Rated to 2.5 Amps and 100 Volts, DC SMA Connector FMBT1630

The information contained in this document is accurate to the best of our knowledge and representative of the part

URL: https://www.fairviewmicrowave.com/sma-bias-tee-10-mhz-12-ghz-2500-ma-100-volts-dc-fmbt1630-p.aspx

described	herein. It may	y be necessar	y to ma	ke modification	ns to the part a	and/or t	he documentation of the	part, in order
to implem	ent improveme	ents. Fairview	Microw	ave reserves	the right to mak	e such	changes as required. Unl	ess otherwise
							resentation or warranty	
					urpose, and Fair	view Mi	crowave does not assum	e any liability
arising out	t of the use of	any part or do	ocument	ation.				

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





