



# Low PIM 7/16 DIN Male to QMA Female Plenum Cable SPP-250-LLPL Coax with LF Solder

The 7/16 DIN male to QMA female cable using SPP-250-LLPL coax, part number FMCA1791, from Fairview Microwave is in-stock and ships same day. This Fairview 7/16 DIN to QMA cable assembly has a male to female gender configuration with 50 ohm corrugated SPP-250-LLPL coax. Fairview Microwave's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -150 dBc. The FMCA1791 7/16 DIN male to QMA female cable assembly operates to 5.8 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

## **Electrical Specifications**

Description	Min	Т	ур	Max	Units		
Frequency Range	DC			5.8		GHz	
VSWR				1.4:1			
Velocity of Propagation		76		%			
RF Shielding	100					dB	
Passive Intermodulation				-150		dBc	
Capacitance		27 [88.58]			pF/ft [pF/m]		
Inductance		0.067 [0.22]		uH/ft [uH/m]			
DC Resistance Inner Conductor		3 [9.84]			Ω/1000ft [Ω/Km]		

#### **Performance by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.45	0.7	1	2.5	5.8	GHz
Insertion Loss (Max	.) 0.038	0.048	0.057	0.094	0.148	dB/ft
	0.12	0.16	0.19	0.31	0.49	dB/m

**Electrical Specification Notes:** 

Insertion loss does not include the loss of the connectors. Insertion loss is estimated as 0.04\*SQRT(FGHz) dB per connector.

### **Mechanical Specifications**

## **Cable Assembly**

Length\* 0 in [0 mm]

Cable

Cable Type SPP-250-LLPL Impedance 50 Ohms Inner Conductor Type Solid Inner Conductor Material and Plating Copper



# **Configuration:**

- 7/16 DIN Male
- OMA Female
- SPP-250-LLPL


## Features:

- Max Frequency 5.8 GHz
- Low PIM: -150 dBc Max
- Shielding Effectivity > 100 dB
- 76% Phase Velocity
- FEP Jacket
- IP67 (Mated)
- Low Loss with Excellent VSWR
- PIM Test Results Marked on Each Cable
- UL910 Plenum Rated Cable
- Extremely Flexible and Lightweight

# **Applications:**

- General Purpose
- Laboratory Use
- Low PIM Applications
- DAS
- Mobile Networks
- In-Building Wireless
- Small Cells
- PIM Testing

# **Cable Diagram:**



Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Dielectric Type Number of Shields Outer Conductor Material and Plating Jacket Material

Jacket MaterialFEP, BlueJacket Diameter0.28 in [7.11 mm]

One Time Minimum Bend Radius 1.25 in [31.75 mm]
Bending Moment 0.8 lbs-ft [1.08 N-m]

#### **Connectors**

Description	Connect	or 1	Connector	Connector 2	
Туре	7/16 DIN	Male	QMA Femal	e	
Impedance	50 Ohn	าร	50 Ohms		
Contact Material & Plating	Brass, Sil	ver	Brass, Silve	r	
Dielectric Type	PTFE		PTFE		
Outer Cond Material & Plat	ing		Brass, Tri-Me	tal	
Body Material & Plating	Brass, Tri-I	Metal	Brass, Tri-Me	tal	
Coupling Nut Material & Pla	ting Brass, Tri-I	Metal			

PTFE

Copper

1

**Environmental Specifications** 

Temperature

Operating Range -55 to +165 deg C

**Compliance Certifications** (see product page for current document)

## **Plotted and Other Data**

Notes:

### **How to Order**

Part Number Configuration:



Example: FMCA1791-12 = 12 inches long cable

FMCA1791-100cm = 100 cm long cable

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020

REV 1.0 Page 2 of 4





Low PIM 7/16 DIN Male to QMA Female Plenum Cable SPP-250-LLPL Coax with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Low PIM 7/16 DIN Male to QMA Female Plenum Cable SPP-250-LLPL Coax with LF Solder FMCA1791


URL: https://www.fairviewmicrowave.com/7-16-din-male-qma-female-cable-spp250llpl-coax-fmca1791-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







STANDARD TOLERANCES

.X ±0.2 .XX ±0.01 .XXX ±0.005

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

Fairview Microwave	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].						
Low PIM 7/16 DIN Male to QMA Female Plenum Cable SPP-250-LLPL Coax with LF Solder	DWG NO FMCA1791				CAGE CODE 3FKR5		
	CAD FILE 12/27/18	SHEET 1 OF 1	SCAL	E N/A	SIZE A	CN2379	