

N Male to SMA Male Cable LMR-200-FR Coax

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.35:1	
Velocity of Propagation		83		%
RF Shielding	90			dB
Capacitance		24.5 [80.38]		pF/ft [pF/m]
Inductance		0.061 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		5.36 [17.59]		$\Omega/1000ft$ [Ω/Km]
DC Resistance Outer Conductor		5.9 [19.36]		$\Omega/1000ft$ [Ω/Km]

Mechanical Specifications

Cable Assembly

Diameter	0.89 in [22.61 mm]
Weight	0.09656 lbs [43.8 g]

Cable

Cable Type	LMR-200-FR
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Tinned Copper
Shield Layer 2	Aluminum Tape
Jacket Material	PE, Black
Jacket Diameter	0.195 in [4.95 mm]

Connectors

Description	Connector 1	Connector 2
Type	N Male	SMA Male
Polarity	Standard	Standard
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Beryllium Copper, Gold	Brass, Gold
Contact Plating Spec.		50 μ in. minimum
Dielectric Type	PTFE	PTFE
Hex Size	13/16 inch	5/16 inch
Torque		4 in-lbs [0.45 Nm]
Body Material & Plating	Brass, Tri-Metal	Brass, Gold
Body Plating Spec.		3 μ in. minimum

Environmental Specifications

Temperature

Operating Range	-40 to +85 deg C
-----------------	------------------



Configuration:

- N Male
- SMA Male
- LMR-200-FR


Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data



How to Order

Part Number Configuration:

FMC0102202 - xx uu

cm = Centimeters
 <blank> = Inches
 Length


Example: FMC0102202-12 = 12 inches long cable
 FMC0102202-100cm = 100 cm long cable

N Male to SMA Male Cable LMR-200-FR Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [N Male to SMA Male Cable LMR-200-FR Coax FMC0102202](#)

URL: <https://www.fairviewmicrowave.com/standard-n-male-sma-male-cable-lmr200fr-coax-fmc0102202-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE N Male to SMA Male Cable LMR-200-FR Coax		DWG NO FMC0102202		CAGE CODE 3FKR5	
CAD FILE	101014	SHEET		SCALE	N/A
				SIZE	A
					5568