

SMA Male to N Female Cable LMR-400 Coax with Times Microwave Connectors

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		2.5	GHz
VSWR			1.35:1	
Velocity of Propagation		85		%
RF Shielding	90			dB
Capacitance		23.9 [78.41]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		1.39 [4.56]		$\Omega/1000ft$ [Ω/Km]
DC Resistance Outer Conductor		1.65 [5.41]		$\Omega/1000ft$ [Ω/Km]

Mechanical Specifications

Cable Assembly

Diameter	0.66 in [16.76 mm]
Weight	0.12743 lbs [57.8 g]

Cable

Cable Type	LMR-400
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Aluminum
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Tinned Copper
Shield Layer 2	Aluminum Tape
Jacket Material	PE, Black
Jacket Diameter	0.405 in [10.29 mm]

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	N Female
Polarity	Standard	Standard
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Brass, Gold	Beryllium Copper, Gold
Contact Plating Spec.	50 μ " Min	
Dielectric Type	Teflon	Teflon
Outer Cond Material & Plating		Brass, Nickel
Hex Size	5/16 inch	
Body Material & Plating	Brass, Nickel	Brass, Nickel

Environmental Specifications

Temperature

Operating Range	-40 to +85 deg C
-----------------	------------------



Configuration:

- SMA Male
- N Female
- LMR-400


Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data



How to Order

Part Number Configuration:

FMC0206400 - xx uu

cm = Centimeters
 <blank> = Inches
 Length


Example: FMC0206400-12 = 12 inches long cable
 FMC0206400-100cm = 100 cm long cable

SMA Male to N Female Cable LMR-400 Coax with Times Microwave Connectors from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [SMA Male to N Female Cable LMR-400 Coax with Times Microwave Connectors FMC0206400](#)

URL: <https://www.fairviewmicrowave.com/sma-male-n-female-cable-times-lmr-400-coax-fmc0206400-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE SMA Male to N Female Cable LMR-400 Coax with Times Microwave Connectors		DWG NO FMC0206400		CAGE CODE 3FKR5	
CAD FILE	101514	SHEET	SCALE	N/A	SIZE A 5568