

FMCA1604 DATA SHEET

Slide-On BMA Jack 2 Hole Flange to TNC Male Cable RG405 Type .086 Coax

The BMA jack slide-on 2 hole flange to TNC male cable using RG405 type .086 coax, part number FMCA1604, from Fairview Microwave is in-stock and ships same day. This Fairview BMA to TNC cable assembly has a jack to male gender configuration with 50 ohm semi-rigid FM-SR086CU coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA1604 BMA jack to TNC male cable assembly operates to 6 GHz. Our RF cable assembly with BMA 2 hole flange interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	Units
Frequency Range	DC			6	GHz
VSWR				1.5:1	
Return Loss				15.56	dB



Configuration:

- Slide-On BMA Jack 2 Hole Flange
- TNC Male
- FM-SR086CU

Features:

• Max Frequency 6 GHz

Applications:

- General Purpose
- Laboratory Use
- Rack and Panel
- BMA Cable RF Backplanes
- Phased Array Interconnects
- High Speed Switching Networks
- Blind Mate BMA Test

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	6	GHz
Insertion Loss (Typ.)	0.1	0.15	0.22	0.33	0.56	dB/ft
	0.33	0.49	0.72	1.08	1.84	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly	
Diameter	

Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Outer Conductor Material and Plating

Repeated Minimum Bend Radius

0.75 in [19.05 mm]

FM-SR086CU 50 Ohms Solid Copper Clad Steel, Silver PTFE 1 Copper

0.05 in [1.27 mm]

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Connectors

Description	Connector 1	Connector 2		
Туре	BMA Jack	TNC Male		
Mount Method	2 Hole Flange			
Impedance	50 Ohms	50 Ohms		
Connection Method	Slide-On			
Contact Material & Plating	Beryllium Copper, Gold	Brass, Gold over Nicke		
Contact Plating Spec.	51.18µ in. minimum			
Dielectric Type	PTFE	PTFE		
Outer Cond Material & Plating	Beryllium Copper, Gold			
Body Material & Plating	Stainless Steel, Gold	Brass, Nickel		
Body Plating Spec.	19.68µ in. minimum			
Coupling Nut Material & Plating		Brass, Nickel		

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or $\pm 3/8''$, whichever is greater.

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:










Typical Performance Data



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689






Slide-On BMA Jack 2 Hole Flange to TNC Male Cable RG405 Type .086 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Slide-On BMA Jack 2 Hole Flange to TNC Male Cable RG405 Type .086 Coax FMCA1604


URL: https://www.fairviewmicrowave.com/bma-jack-tnc-male-cable-rg405-type-.086-coax-fmca1604-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL, 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
Slide-On BMA Jack 2 Hole Flange to TNC Male Cable RG405 Type .086 Coax	dwg no FMCA1604			CAGE CODE 3FKR5		
	CAD FILE 12/19/17	SHEET	SCAL	_E N/A SIZE A	CN2245	

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689