



Snap-On BMA Jack to TNC Male Cable LMR-100 Coax

The BMA jack snap-on to TNC male cable using LMR-100 coax, part number FMCA1646, from Fairview Microwave is in-stock and ships same day. This Fairview BMA to TNC cable assembly has a jack to male gender configuration with 50 ohm flexible LMR-100A-PVC coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA1646 BMA jack to TNC male cable assembly operates to 2.5 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	ι	Inits		
Frequency Range	DC			2.5		GHz		
VSWR				1.4:1				
Return Loss				15.56		dB		
Velocity of Propagation		6	66			%		
RF Shielding	90					dB		
Group Delay		1.54	[5.05]		ns/f	t [ns/m]		
Capacitance		30.8 [101.05]	pF/f	t [pF/m]		
Inductance		0.077	0.077 [0.25]			uH/ft [uH/m]		
DC Resistance Inner Conductor			81 [265.75]		$\Omega/1000$ ft [$\Omega/$ Km]			
DC Resistance Outer Conductor		9.5 [31.17]		Ω/100	0ft [Ω/Km]		
Jacket Spark				2,000	\	/rms		

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	2.5	GHz
Insertion Loss (Typ.)	0.07	0.12	0.16	0.24	0.4	dB/ft
	0.23	0.39	0.52	0.79	1.31	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Diameter 0.6 in [15.24 mm]

Cable

Cable Type Impedance LMR-100A-PVC 50 Ohms

Configuration:

- Snap-On BMA Jack
- TNC Male
- LMR-100A-PVC

Features:

- Max Frequency 2.5 GHz
- Shielding Effectivity > 90 dB
- 66% Phase Velocity
- · Double Shielded
- PVC Jacket

Applications:

- General Purpose
- · Laboratory Use
- Rack and Panel
- BMA Cable RF Backplanes
- Phased Array Interconnects
- High Speed Switching Networks
- Blind Mate BMA Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (97

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields Shield Layer 1 Shield Layer 2 Jacket Material

Jacket Diameter

One Time Minimum Bend Radius Repeated Minimum Bend Radius

Bending Moment Flat Plate Crush Tensile Strength Solid

Copper Clad Steel

PE 2

> Aluminum Tape Tinned Copper Braid

PVC, Black

0.11 in [2.79 mm]

0.25 in [6.35 mm] 1 in [25.4 mm]

15 lbs [6.8 Kg]

0.1 lbs-ft [0.14 N-m] 10 lbs/in [0.18 Kg/mm]

. .

Connectors

Description	Connect	or 1		Connector 2				
Туре	BMA Ja	ck		TNC Male				
Impedance	50 Ohn	ns		50 Ohms				
Connection Method	Snap-C)n						
Contact Material & Plating	Beryllium Copper, Gold			old Beryllium Copper, Gol				
Contact Plating Spec.	51.18µ in. m	inimur	n					
Dielectric Type	PTFE			Teflon				
Outer Cond Material & Plati	ing Beryllium Cop	per, G	old					
Body Material & Plating	Passivated Stair	nless S	iteel	el Brass, Silver				
Coupling Nut Material & Pla	nting			Brass, Silver				

Mechanical Specification Notes:

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:


301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

^{*}All cable assemblies have a length tolerance of 1.5% or \pm 3/8", whichever is greater.





Typical Performance Data



How to Order

Part Number Configuration: FMCA1646 - xx uu



Example: FMCA1646-12 = 12 inches long cable

FMCA1646-100cm = 100 cm long cable





Snap-On BMA Jack to TNC Male Cable LMR-100 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Snap-On BMA Jack to TNC Male Cable LMR-100 Coax FMCA1646


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order

URL: https://www.fairviewmicrowave.com/bma-jack-tnc-male-cable-lmr100-coax-fmca1646-p.aspx

to implem	ent improver	ments. Fairview	Microw	ave reserv	es the righ	nt to mak	ke such	changes	as req	uired. U	nless	othe	rwise
		ns are nominal.											
		described hereir			purpose,	and Fair	view M	icrowave	does	not assu	me a	ny lia	ability
arising ou	t of the use o	of any part or do	cument	tation.									







STANDARD TOLERANCES ,X ±0.2 ,XX ±0.01 ,XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL, 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME, 3. DIMENSIONS ARE IN INCHES [mm].					
Snap-On BMA Jack to TNC Male Cable LMR-100 Coax	DWG NO FMCA1646			CAGE CODE	3FKR5	
	CAD FILE 12/29/17	SHEET	SCAL	LE N/A SIZE A	CN2245	