

## N Female Bulkhead to TNC Female Cable in 60 Inch Length Using RG223 Coax

The type N female bulkhead to TNC female cable using RG223 coax, part number FMCA2775-60, from Fairview Microwave is in-stock and ships same day. This Fairview type N to TNC cable assembly has a female to female gender configuration with 50 ohm flexible RG223 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. Our RF cable assembly with type N bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

Description	Min	Typ	Max	Units
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]

### Mechanical Specifications

#### Cable Assembly

Length*	60 in [152.4 cm]
Weight	0.247 lbs [112.04 g]

#### Cable

Cable Type	RG223
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.21 in [5.33 mm]

One Time Minimum Bend Radius	1 in [25.4 mm]
------------------------------	----------------



### Configuration:

- N Female Bulkhead
- TNC Female
- RG223

### Features:

- 66% Phase Velocity
- Double Shielded
- PVC Jacket

### Applications:

- General Purpose
- Laboratory Use

Fairview Microwave  
301 Leora Ln., Suite 100  
Lewisville, TX 75056  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

## Connectors

Description	Connector 1	Connector 2
Type	N Female	TNC Female
Mount Method	Bulkhead	
Specification	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Brass, Gold	
Contact Plating Spec.	30μ in. minimum	
Dielectric Type	Teflon	
Body Material & Plating	Brass, Nickel	Brass, Nickel
Body Plating Spec.	100μ in. minimum	

**Compliance Certifications** (see [product page](#) for current document)

## Plotted and Other Data

Notes:

- Values at 25°C, sea level.

## How to Order

Part Number Configuration:

**FMCA2775 - xx uu**

cm = Centimeters  
 <blank> = Inches

Length

Example: FMCA2775-12 = 12 inches long cable  
 FMCA2775-100cm = 100 cm long cable


N Female Bulkhead to TNC Female Cable in 60 Inch Length Using RG223 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [N Female Bulkhead to TNC Female Cable in 60 Inch Length Using RG223 Coax FMCA2775-60](#)

URL: <https://www.fairviewmicrowave.com/n-female-bulkhead-to-tnc-female-cable-rg223-coax-in-60-inch-and-rohs-fm-ca2775-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	02/21/2022	AGANWANI



**NOTES:**

1. CABLES 36" AND UNDER HAVE 1 LABEL CENTERED.  
CABLES OVER 36" HAVE 2 LABELS, ONE AT EACH END  
6.0" FROM THE FRONT OF THE CONNECTOR.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

<p><b>Fairview Microwave</b> an INFINITE brand</p>		<p>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS</p>		<p>THIRD-ANGLE PROJECTION</p>	
<p>TITLE</p>		<p>TOLERANCES:</p>		<p>CABLE LENGTH (L) TOLERANCES:</p>	
<p>N Female Bulkhead to TNC Female Cable in 60 Inch Length Using RG223 Coax</p>		<p> <math>.X = \pm .2</math> [5.08] FRACTIONS  <math>.XX = \pm .02</math> [51] <math>\pm 1/32</math>  <math>.XXX = \pm .005</math> [13] ANGLES <math>\pm 1^\circ</math> </p>		<p> <math>L \leq 12</math> [305] = <math>\pm 1</math> [25] / -0  <math>12</math> [305] &lt; <math>L \leq 60</math> [1524] = <math>\pm 2</math> [51] / -0  <math>60</math> [1524] &lt; <math>L \leq 120</math> [3048] = <math>\pm 4</math> [102] / -0  <math>120</math> [3048] &lt; <math>L \leq 300</math> [7620] = <math>\pm 6</math> [152] / -0  <math>300</math> [7620] &lt; <math>L = +5\%L</math> / -0                 </p>	
<p>ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.</p>		<p>SCALE</p>		<p>SHEET 1 OF 1</p>	
<p>SIZE A</p>		<p>CAGE CODE 3FKR5</p>		<p>ITEM NO. FMCA2775</p>	
<p>DRAWN BY MVEERAPPAN</p>		<p>REV A</p>		<p>N/A</p>	

T-Rev.D