

FMCN1508 DATA SHEET

2.92mm Male Connector Solder Attachment for FMBC005, FMBC006 Cable Low Loss 086 Semi-Rigid

2.92mm male connector with solder attachment for FMBC005 and FMBC006, part number FMCN1508, from Fairview Microwave is in-stock and ships same day.

Fairview's 2.92mm male connector FMCN1508 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Тур	Max	Units
VSWR			1.14:1	
DWV (AC)			1,000	Vrms
High Potential Voltage			670	Vrms
Corona Discharge			250	Vrms
Insulation Resistance	5,000			MOhms
RF Leakage	-90			dB

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Freq. Range	DC to 18	18 to 26.5	26.5 to 45			GHz
VSWR, Max	1.1:1	1.12:1	1.14:1			

Electrical Specification Notes: Insertion Loss = 0.04*SQRT(Fghz) dB

Mechanical Specifications

Size

 Length
 0.55 in [13.97 mm]

 Width/Dia.
 0.35 in [8.89 mm]

 Weight
 0.01 lbs [4.54 g]

Mating Cycles 500 Cycles

Mating Torque 8 to 10 in-lbs [0.90 to 1.13 Nm]

Material Specifications

Description	Material	Plating				
Contact	Beryllium Copper	Gold ASTM-B488				
Insulation	PTFE					
Body	Beryllium Copper	Gold ASTM-B488				



Configuration:

- 2.92mm Male Connector
- 50 Ohms
- Straight Body Geometry
- FMBC005, FMBC006 Interface Type
- Solder Attachment

Features:

- Excellent VSWR of 1.14:1
- Gold Plated Beryllium Copper Contact
- Contact plating according to ASTM-B488

Applications:

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Coupling Nut	Steel	
Gasket	Silicone Rubber	

Environmental Specifications

Temperature

Operating Range Shock Vibration

Thermal Shock

-65 to +165 deg C

MIL-STD-202, Method 213, Condition I MIL-STD-202, Method 204, Condition D MIL-STD-202, Method 107, Condition B

Compliance Certifications (see product page for current document)


Plotted and Other Data

Notes:





Assembly Instruction




STEP 1:

- PRE-TIN CABLE OUTER JACKET OVER APPROX. LENGTH SHOWN.
- TRIM CABLE TO EXPOSE CENTER CONDUCTOR AS SHOWN.
 - POINT CENTER CONDUCTOR AS INDICATED.

STEP 2:

INSERT CABLE INTO CONNECTOR UNTIL CENTER CONDUCTOR PLUGS IN AND CABLE SEATS IN CONNECTOR BORE.

SOLDER CABLE JACKET TO BODY WHERE SHOWN APPLYING HEAT TO







2.92mm Male Connector Solder Attachment for FMBC005, FMBC006 Cable Low Loss 086 Semi-Rigid from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 2.92mm Male Connector Solder Attachment for FMBC005, FMBC006 Cable Low Loss 086 Semi-Rigid FMCN1508


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order


URL: https://www.fairviewmicrowave.com/2.92mm-male-fmbc005-fmbc006-connector-fmcn1508-p.aspx

to implem	nent improvements.	. Fairview	Microwa	ave reserve	es the righ	it to mak	e such	changes i	as requ	iired. Unles	ss otl	herwise
stated, al	specifications are	nominal.	Fairvie	v Microwa	e does n	ot make	any rep	resentat	ion or 1	warranty re	gard	ling the
suitability	of the part describ	oed herein	for any	particular	purpose,	and Fair	view Mi	crowave	does n	ot assume	any	liability
arising ou	t of the use of any	part or do	cument	ation.								













STANDARD TOLERANCES
.X ±0.2

.XX ±0.01 .XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

NOTES: DISTANCE FROM END OF CABLE CENTER COND. TO REF. PL. IS .235

Fairview Microwave	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].								
2.92mm Male Connector Solder Attachment for	DWG NO FMCN1508					CAGE CODE 3FKR5			
FMBC005, FMBC006 Cable Low Loss 086 Semi-Rigid	CAD FILE	01/11/19	SHEET	1 OF 1	SCAL	E N/A	SIZE A	CN2379	