



# 2 Way Power Splitter 1.0 mm Connectors From DC to 110 GHz Rated at 0.2 Watts

Fairview Microwave carries a wide selection of power dividers to fit your needs. These components are essential in many systems, allowing the combination of multiple signals or splitting of a single signal into multiple signals with equal magnitude and phase. Fairview Microwave's resistive and Wilkinson power dividers come with excellent performance featuring minimal loss, high isolation and low VSWR. They are available in both narrow and broad bandwidths with a variety of connector types such as 2.92mm, BNC, N, SMA and 1.0 mm (W1). The FMDV2108 is a 2-way resistive power splitter that operates from DC to 110 GHz and can handle up to 0.2 Watt (CW) with 9.5 dB max insertion loss. The package interface uses 1.0 mm (W1) female connectors for the output and a 1.0 mm (W1) male connector for the input.



Design Number of Output Ports Resistive

Description	Min	Тур	Max	Units
Frequency Range	DC		110	GHz
Impedance		50		Ohms
Input VSWR			2.1:1	
Insertion Loss			9.5	dB
Input Power (CW)			0.2	Watts

#### **Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Freq. Range	DC-20	20-50	50-67	67-105	105-110	GHz
In VSWR, Max	1.2:1	1.4:1	1.4:1	1.9:1	2.1:1	
IL, Max	7	7.5	8.25	9	9.5	dB
Output Match, M	lin 18	14	14	8	6	dB
Amp Balance, M	ax 0.4	0.4	0.4	1	1	dB

Electrical Specification Notes:

Insertion loss max 9.5 dB, Includes Power Dividing Loss.

## **Mechanical Specifications**

# Size

Size	
Length	0.441 in [11.2 mm]
Width	0.441 in [11.2 mm]
Height	0.441 in [11.2 mm]
Weight	0.05 lbs [22.68 g]

#### Configuration

Input Connector 1.0mm Male
Output Connectors 1.0mm Female



#### **Features:**

- 2-Way Power Splitter
- DC to 110 GHz Frequency Range
- 1.0 mm (W1) Connectorized Design
- Max Power 0.2 Watt (CW)
- Insertion Loss < 9.5 dB
- Typical VSWR of 1.6:1

# **Applications:**

- Test and Measurement
- Military Communications
- Commercial Communications
- Wireless Communications
- SATCOM

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





# **Environmental Specifications Temperature**

Operating Range

Storage Range

Humidity Shock +0 to +70 deg C -55 to +125 deg C

95% at 40 °C, 96 hours, Test 103B, Condition B 100 G peak sawtooth, method 213, Condition B

**Compliance Certifications** (see product page for current document)

### **Plotted and Other Data**

Notes:

2 Way Power Splitter 1.0 mm Connectors From DC to 110 GHz Rated at 0.2 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 2 Way Power Divider 1.0mm Interface from DC to 110 GHz Rated at 0.2 Watts FMDV2108

URL: https://www.fairviewmicrowave.com/0-way-power-divider-1.0mm-110-ghz-fmdv2108-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020 REV 1.0 Page 2 of 3





