



SMA Frequency Divider Divide by 4 Prescaler Module Operating from 100 MHz to 13 GHz

The FMFD4003 is a coaxial packaged Frequency Divider module that operates across a wide input frequency range from 100 MHz to 13 GHz and supports a divide ratio of 4. Output Frequency is 25 MHz to 3.25 GHz. Impressive broadband typical performance of this Prescaler includes output power of +5 dBm and SSB phase noise of -151 dBc/Hz at 100 kHz offset. This exceptional technical performance is achieved through the use of a hybrid MIC PCB solder assembly which is RoHS and REACH compliant. This frequency divider design requires +12 Vdc typical bias voltage, operates over maximum temperature range of -40°C to +85°C, and has an absolute maximum rating for input power of +13 dBm. The rugged and compact package supports SMA Female connectors, RFI and Ground Pins. For highly reliable operation, the model is guaranteed to meet MIL-STD-202 environmental test conditions for Humidity, Shock, Vibration, and Altitude.

Electrical Specifications (TA= 25°C, Vd1 = 12 Vdc, Id1 = 120 mA)

Description	Min	Тур	Max	Units
Input Frequency (Sine Wave) 0.1			13	GHz
Output Frequency (Square Wave Output) 0.025			3.25	GHz
Output Power	2	5		dBm
Phase Noise @100kHz Offset		-151		dBc/Hz
Operating DC Voltage 1	7	12	15	V
Operating DC Current 1		120		mA

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	0.1 to	1 1 to 8	8 to 11	11 to 13		GHz
Input Power (CW), Max	10	10	5	3		dBm
Input Power (CW), Typ	0	0	0	0		dBm
Input Power (CW), Min	-3	-15	-10	-5		dBm

Mechanical Specifications

Size

 Length
 1.25 in [31.75 mm]

 Width
 1.25 in [31.75 mm]

 Height
 0.563 in [14.3 mm]

 Output Connector
 SMA Female

Environmental Specifications

Temperature

Vibration

Operating Range -40 to +85 deg C
Storage Range -55 to +125 deg C
Humidity MIL-STD-202F, Method 103B, Condition B
Shock MIL-STD-202F, Method 213B, Codition B

MIL-STD-202F, Method 204D, Condition B



Features:

- Wide Input Frequency Range:
 100 MHz to 13 GHz
- Divide-by-4 Prescaler
- Output Frequency 25 MHz to 3.25 GHz
- Output Power: +5 dBm typical
- Low SSB Phase Noise: -151 dBc/ Hz @ 100 KHz offset typical
- RoHS & REACH Compliant Assembly
- Bias Voltage: +12 Vdc
- Operational Temperature Range: -40°C to +85°C
- Compact SMA Connectorized Package
- Designed to meet MIL-STD-202 Test Conditions

Applications:

- PLL Applications
- Test Instrumentation
- Countermeasures
- Point to Point Microwave Radio
- SATCOM
- MILCOM
- Base Stations

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





Altitude


MIL-STD-202F, Method 105C, Condition B

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data



SMA Frequency Divider Divide by 4 Prescaler Module Operating from 100 MHz to 13 GHz from Fairview Microwave is instock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: SMA Frequency Divider Divide by 4 Prescaler Module Operating from 100 MHz to 13 GHz FMFD4003

URL: https://www.fairviewmicrowave.com/sma-frequency-divider-divide-4-prescaler-module-100-mhz-13-ghz-fmfd4003-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







TITLE DWG NO CAGE CODE FMFD4003 3FKR5 SMA Frequency Divider Divide by 4 Prescaler Module Operating from 100 MHz to 13 GHz CAD FILE 04/26/18 SHEET 1 OF 1 SCALE N/A SIZE A 7361

an INFINIT[®] brand