



# 7/16 DIN SOLT VNA Calibration Kit up to 7.5 GHz, Including Short Circuit, Open Circuit, Load, and Thru

Fairview Microwave's 7/16 DIN 7.5 GHz VNA calibration kit is used to calibrate a Vector Network Analyzer (VNA) and associated test setup, thus removing the test instrumentations influence on the device under test (DUT) and allowing the best possible error-free characterization of the DUT. The FMCK1022 SOLT cal kit includes 7/16 DIN male and female fully-characterized Short Circuits, Open Circuits, Fixed Loads, and Thrus used in a standard multi-port VNA calibration process. In addition to the RF calibration standards, a fixed torque break-over style torque wrench and a set of open-ended wrenches are included for use in mating and de-mating calibration components. Component correction factors have also been documented and are supplied in this VNA calibration kit datasheet. The data file may be downloaded from the FMCK1022 product page on Fairview Microwave's web site or requested by contacting technical support.

A properly performed n-port SOLT calibration allows for full characterization of the VNA test ports. RF calibrations performed using high-quality VNA test cables effectively extends the vector network analyzer test ports to the end of the cables, and this allows for greater flexibility when characterizing a product under test.

Available in-stock and ships same day!

#### Configuration

Connector Frequency Range 7/16 DIN DC to 7.5 GHz



#### **Features:**

- · SOL or SOLT versions available
- Cal kit definition files for Keysight, Rohde & Schwarz, and Anritsu VNAs
- Works with all major VNAs
- Protective wooden case for safe storage of components
- Torque wrench and tools included

#### **Applications:**

- Calibration of Vector Network Analyzers
- Research and development
- Aerospace and defense
- · Production test environments

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





### Electrical Specifications for FMCK1022 7/16 DIN Devices

Item	Part Number	Specifications	Frequency (GHz)
Female Termination	FMTR1061	1.02 Max VSWR	DC to 4
Male Termination	FMTR1062	1.03 Max VSWR	4 to 7.5
Female Short  Male Short	FMSC3016 FMSC3017	±0.85° deviation from nominal	DC to 7.5
Female Open Male Open	FMSC3031 FMSC3032	±1.25° deviation from nominal	DC to 7.5
Adapter Thru Female Thru Female to Male	FMAD1132 FMAD1134	1.03 Max VSWR	DC to 7.5
Thru Male	FMAD1133		
Torque Wrench	ST-D-27MM-B20	20 in-lb Torque Setting	
Open End Wrench	FMTL1003	9/16" x 9/16" Dimensions	





#### FMSC3016 7/16 DIN Female Short



ELECTRICAL				
Frequency Range	DC to 7.5	GHz		
Phase	DC to 4GHz ±0.6°	Max		
Pilase	4 to 7.5 GHz ±0.85°	Max		
Offset Impedance	50	Ω		
Offset Loss	0.63	GΩ/s		
Electrical Delay	66.734	nS		
	L0 x 10^-12 = 0.0	Н		
Inductance	L1 x 10^-24 = 0.0	H/Hz		
inductance	L2 x 10^-33 = 0.0	H/Hz^2		
	L3 x 10^-42 = 0.0	H/Hz^3		

	MECHANICAL	
Housing	Stainless Steel	
Connector	7/16 DIN Female	
Screw Thread	M29 x 1.5-6G	
Dimensions	1.050 [26.67]Ø, 1.62 [41.14] Lengt	:h
Pin Depth	0.0697 + 0.0015/0	





#### FMSC3017 7/16 DIN Male Short Specifications



ELECTRICAL				UNIT
Frequency Range	ė	DC to 7.	5	GHz
Phase		DC to 4GHz	±0.6°	Max
Pilase		4 to 7.5 GHz	±0.85°	Max
Offset Impedance	Offset Impedance		50	
Offset Loss	Offset Loss		0.63	
Electrical Delay		66.734		nS
		L0 x 10^-12 = 0.0		Н
Inductance		L1 x 10^-24 = 0.0		H/Hz
		L2 x 10^-33 = 0.0		H/Hz^2
		L3 x 10^-42	= 0.0	H/Hz^3

Housing	Stainless Steel			
Connector	7/16 DIN Male			
Screw Thread	M29 x 1.5-6G			
Dimensions	1.311 [33.29]Ø, 1.98 [50.2	9] Length		
Pin Depth	0.0697 + 0.0015/0			





### FMSC3031 7/16 DIN Female Open Specifications



ELECTRICAL					UNIT
Frequency Rang	ge	DC to	o 7.5	5	GHz
Phase		DC to 4GH	łz	±1.0°	Max
Filase		4 to 7.5 G	Hz	±1.25°	Max
Offset Impedance	Offset Impedance		50		Ω
Offset Loss		0.63		GΩ/s	
Electrical Delay		66.734			pS
		C0 x 10^	-15	= 32	F
Capacitance		C1 x 10^	-27	= 0.0	F/Hz
		C2 x 10^	-36	= -50	F/Hz^2
		L3 x 10^-	45 =	100	F/Hz^3

	MECHANICAL
Housing	Stainless Steel
Connector	7/16 DIN Female
Screw Thread	M29 x 1.5-6G
Dimensions	1.141 [28.98]Ø, 2 [50.28] Length
Pin Depth	0.0697 + 0.0015/0 [1.77038]





### FMSC3032 7/16 DIN Male Open Specifications



_					
L	ELECTRICAL				
	Frequency Ran	ge	DC to 7	.5	GHz
	Phase		DC to 4GHz	±1.0°	Max
	Pilase		4 to 7.5 GHz	±1.25°	Max
ſ	Offset Impedance		50		Ω
Ī	Offset Loss	Offset Loss 0.63		GΩ/s	
ſ	Electrical Delay		66.734		pS
	Capacitance		C0 x 10^-15 = 32		F
			C1 x 10^-27 = 0.0		F/Hz
			C2 x 10^-36 = -50		F/Hz^2
			L3 x 10^-45	= 100	F/Hz^3

	MECHANICAL	
Housing	Stainless Steel	
Connector	7/16 DIN Male	
Screw Thread	M29 x 1.5H-6H	
Dimensions	1.311 [33.29]Ø, 2.31 [58.6	[57] Length
Pin Depth	0.0697 + 0.0015/	0





#### FMTR1061 7/16 DIN Female Termination Specifications



	ELETRICAL				UNIT	
Frequency	Ran	ge	DC to 7.5		GHz	
\/S\\/P at Eroqui	SWR at Frequency Range	Pango	DC to 4 G	Hz	1.02	Max
v 3 v v n at Flequi	ency	ilcy Kange	4 to 7.5 G	iHz	1.03	Max
Impedance		5	0		Ω	
Dawer Dating			3 wa	tt C\	Ν	
Power Rating		1kW	Pea	ık		

	MECHANICAL
Housing	Stainless Steel/Aluminum
Connector	7/16 DIN Female
Screw Thread	M29 x 1.5-6G
Dimensions	1.05 [26.67]Ø, 2.758 [70.05] Length
Pin Depth	0.0682 - 0.0697





#### FMTR1062 7/16 DIN Male Termination Specifications



ELETRICAL					UNIT		
Frequency	Frequency Range			DC to 7.5		GHz	
VSWR at Frequ	ency		Pango	DC to 4 G	Hz	1.02	Max
v 3 v v at Frequ		ncy kange	4 to 7.5 G	Hz	1.03	Max	
Impedance		5	0		Ω		
Dower Poting			3 watt CW				
Power Rating		1kW	Pea	ak			

	MECHANICAL
Housing	Stainless Steel/Aluminum
Connector	7/16 DIN Male
Screw Thread	M29 x 1.5H-6H
Dimensions	0.985 [25.019]Ø, 3.068 [77.927] Length
Pin Depth	0.0697 + 0.0015/0





# FMAD1132 7/16 DIN Thru Female Specifications



	ELECTRICAL		Unit		
	Frequency Range		DC to 7.5		GHz
VSWR at Frequency Range		DC to 7.5	GHz	1.03	Max
Impedance			50		Ω
Typical Delay		1	L66		ps

	MECHANICAL
Housing	Stainless Steel
Connector	7/16 DIN Female to 7/16 DIN Female
Screw Thread	M29 x 1.5-6G
Dimensions	1.050 [26.67]Ø, 1.83 [46.48] Length
Pin Depth	0.0697 + 0.0015/-0.0015





## FMAD1133 7/16 DIN Thru Male Specifications



ELECTRICAL		
Frequency Range	DC to 7.5	GHz
VSWR at Frequency Range	DC to 7.5 GHz 1.03	Max
Impedance	50	Ω
Typical Delay	166	ps

		MECHANICAL	
Housing		Stainless Stee	el
Connector		7/16 DIN Male to 7/16	5 DIN Male
Screw Thread		M29 x 1.5H-6	Н
Dimensions 1.311 [33.29]Ø, 2.54 [64.51] Length		4.51] Length	
Pin Depth 0.0697 + 0.0015/-0.0015		0.0015	





### FMAD1134 7/16 DIN Thru Female to Male Specifications



ELECTRICAL		Unit			
Frequency Range		DC to 7.5			GHz
VSWR at Frequence	cy Range	DC to 7.5	GHz	1.03	Max
Impedance		50		Ω	
Typical Delay		:	166		ps

	MECHANICAL		
Housing	Stainless Steel		
Connector	7/16 DIN Female to 7/16 DIN Male		
Screw Thread	M29 x 1.5H-6H		
Dimensions	1.3 [33.02]Ø, 2.13 [54.10] Length		
Pin Depth	0.0697 + 0.0015/-0		





### **General Instructions and Usage Notes**

#	Notes		
1	Keep provided protective blue caps installed when not in use.		
2	Store in climate controlled environment.		
3	Always keep connectors clean.		
4	Avoid touching the connector interface.		
5	Use caution when handling.		
6	For female components, do not insert male pin greater than 0.037" [.94 mm]. Failure to comply will result in damage to the female connector.		
7	When mating, always ensure that the components to be interconnected remain in a fixed position while rotating <b>only the coupling nut</b> slowly to mate the connectors.		
8	When de-mating, always ensure that the interconnected components remain in a fixed position while rotating <b>only the coupling nut</b> slowly to de-mate the connectors.		
9	Visually inspect the connector threads prior to use. If needed, clean the center conductor pin and outer conductor with alcohol to remove any debris that may be present. Be sure to apply the alcohol in a circular motion with a lint-free cloth or applicator.		
10	Use at room temperature.		

**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:

• Values at 25 °C, sea level





7/16 DIN SOLT VNA Calibration Kit up to 7.5 GHz, Including Short Circuit, Open Circuit, Load, and Thru from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 7/16 DIN SOLT VNA Calibration Kit up to 7.5 GHz, Including Short Circuit, Open Circuit, Load, and Thru FMCK1022

The information contained in this document is accurate to the best of our knowledge and representative of the part

URL: https://www.fairviewmicrowave.com/7-16-din-short-open-load-thru-solt-analyzer-calibration-kit-7.5ghz-fmck1022-p.aspx

