

## RA N Male Precision Connector Clamp/Solder Attachment for LL142 Cable

RA type N male precision connector with clamp/solder attachment for LL142, part number FMCN1082, from Fairview Microwave is in-stock and ships same day. This type N male connector operates up to a maximum frequency of 18 GHz and offers excellent VSWR of 1.16:1. Its right angle body geometry facilitates connections in tight spaces.

Fairview's RA type N male connector FMCN1082 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		18	GHz
VSWR			1.16:1	
Insertion Loss			0.43	dB
Operating Voltage (AC)			250	Vrms
DWV (AC)			750	Vrms
High Potential Voltage 5 to 7.5 MHz			500	Vrms
Corona Discharge at 70,000 ft			190	Vrms
Insulation Resistance	5,000			MOhms
RF Leakage	90			dB

Electrical Specification Notes:  
Insertion loss:  $0.1 \times \sqrt{f(\text{GHz})}$  dB max.  
RF leakage: 90 dB min up to 1 GHz.

### Mechanical Specifications

<b>Size</b>	
Length	1.2 in [30.48 mm]
Width/Dia.	1.14 in [28.96 mm]
Height	0.82 in [20.83 mm]
Weight	0.101 lbs [45.81 g]
Mating Cycles	500 Cycles
Mating Torque	12 to 15 in-lbs [1.36 to 1.70 Nm]

### Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold over Nickel 50 µin minimum



### Configuration:

- N Male Connector
- 50 Ohms
- Right Angle Body Geometry
- LL142 Interface Type
- Clamp/Solder Attachment
- 3/4 Inch Hex
- Precision Design

### Features:

- Operating Frequency of 18 GHz Max.
- Excellent VSWR of 1.16:1
- Gold over Nickel Plated Beryllium Copper Contact
- 50 µin minimum contact plating

### Applications:

- General Purpose Test
- Precision Test & Measurement
- Custom Cable Assemblies

Fairview Microwave  
301 Leora Ln., Suite 100  
Lewisville, TX 75056  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

Insulation	PTFE	
Body	Passivated Stainless Steel	SAE-AMS-2700
Coupling Nut	Passivated Stainless Steel	SAE-AMS-2700


Environmental Specifications

Temperature	-65 to +165 deg C
Operating Range	MIL-STD-202, Method 106, No Vibration
Humidity	MIL-STD-202, Method 213, Condition I
Shock	MIL-STD-202, Method 204, Condition D
Vibration	MIL-STD-202, Method 107, Condition B
Thermal Shock	MIL-STD-202, Method 101, Condition B (5%)
Salt Spray	

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:	
Assembly Instruction	





RA N Male Precision Connector Clamp/Solder Attachment for LL142 Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [RA N Male Precision Connector Clamp/Solder Attachment for LL142 Cable FMCN1082](#)

URL: <https://www.fairviewmicrowave.com/n-male-ll142-connector-fmcn1082-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





**STANDARD TOLERANCES**

.X	±0.2
.XX	±0.01
.XXX	±0.005

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

NOTES:  
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN INCHES [mm].

TITLE RA N Male Precision Connector Clamp/Solder Attachment for LL142 Cable	DWG NO FMCN1082		CAGE CODE 3FKR5			
	CAD FILE	06/11/19	SHEET	1 OF 2	SCALE	N/A
					SIZE	A
						7361