

## Zero Biased Waveguide Detector WR-28 to SMA Female and Negative Video Out From 26.5 GHz to 40 GHz Ka Band, UG-599/U Square Cover Flange

FMMT3005 is an Ka Band Waveguide Detector. The Detector operates in the 26.5 GHz to 40 GHz Frequency Range and has a Negative Output with a Sensitivity of -1000 mV/mW Minimum. The unit operates over a 0°C to +50°C Temperature Range and has a Maximum Input Power Rating of +20 dBm. The Detector has a WR-28 Waveguide with UG-599/U Flange as the RF connector and the DC Output Port uses an SMA Female Connector.

### Electrical Specifications

Description	Min	Typ	Max	Unit
Frequency Range	26.5		40	GHz
Voltage Sensitivity	-1,000			mV/mW
Input Power			+20	dBm

### Mechanical Specifications

#### Temperature

Operating Range

0 to +50 deg C

#### Size

Length

1.24 in [31.5 mm]

Width

1 in [25.4 mm]

Height

0.75 in [19.05 mm]

Weight

0.0625 lbs [28.35 g]

Waveguide Size

WR-28

Flange Destination

UG-599/U

Flange Type

Flange Type

DC Connector

SMA Female

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

- Values at 25 °C, sea level
- ESD Sensitive Material, Transport material in Approved ESD bags. Handle only in approved ESD Workstation.



### Features:


- Frequency: 26.5 GHz to 40 GHz
- Sensitivity: -1000 mV/mW Minimum
- Output: Negative
- Maximum Power Input 20 dBm
- RF Connector WR-28 Waveguide with UG 599/U Flange
- DC Output: SMA Female Connector

### Applications:

- Test Lab
- Military Communications
- Commercial Communications

Fairview Microwave  
301 Leora Ln., Suite 100  
Lewisville, TX 75056  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Typical Performance Data**




Zero Biased Waveguide Detector WR-28 to SMA Female and Negative Video Out From 26.5 GHz to 40 GHz Ka Band, UG-599/U Square Cover Flange from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Zero Biased Waveguide Detector WR-28 to SMA Female and Negative Video Out From 26.5 GHz to 40 GHz Ka Band, UG-599/U Square Cover Flange FMMT3005](https://www.fairviewmicrowave.com/zero-biased-waveguide-detector-wr-28-sma-female-negative-26.5-40-ghz-fmmt3005-p.aspx)

URL: <https://www.fairviewmicrowave.com/zero-biased-waveguide-detector-wr-28-sma-female-negative-26.5-40-ghz-fmmt3005-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



UNLESS OTHERWISE SPECIFIED  
DIMENSIONS ARE IN INCHES.  
TOLERANCES ARE:

DECIMALS	ANGLES	FRACTIONS
.XX ± .01	± 1/2°	± 1/64
.XXX ± .005		

HOLE DIAMETER	TOLERANCE
.0135 TO .125	+.004/-0.001
.126 TO .250	+.005/-0.001
.251 TO .500	+.006/-0.001
.501 TO .750	+.008/-0.001
.751 TO 1.000	+.010/-0.001
1.001 TO 2.000	+.012/-0.001

\* THESE DIMENSIONS AND TOLERANCES  
SUPERSEDE NOTE #1 ON TITLE BLOCK.

**FAIRVIEW MICROWAVE INC.**  
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

**NOTES:**

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

**TITLE**

Zero Biased Waveguide Detector WR-28 to SMA  
Female and Negative Video Out From 26.5 GHz to 40  
GHz Ka Band, UG-599/U Square Cover Flange

**DWG NO**

FMMT3005

**CAGE CODE**

3FKR5

CAD FILE 040615

SHEET

SCALE N/A

SIZE A

2233