

**SP6T Latching 0.05 dB Low Insertion Loss
Repeatability DC to 40 GHz Terminated Relay
Switch, Indicators, Self Cut Off, 5W, 24V, 2.92mm**

The FMSW6332 is a single pole six throw (SP6T) terminated electromechanical switch that operates across a wide frequency range from DC to 40 GHz and has guaranteed insertion loss repeatability of 0.05 dB max over a life span of 5 million switching cycles in a Break Before Make condition. Maximum Insertion loss is 0.9 dB and Isolation is rated up to 60 dB minimum. The model also supports a hot switching limit of up to 1W CW maximum. The Latching Self Cut-Off actuator design includes indicators, a +24 Vdc operating voltage, and operates over a temperature range of -25°C to +75°C. The rugged and compact package assembly supports 2.92mm connectors and an HE10 receptacle, ribbon cable, and HE10 connector for command control capability. And for highly reliable operation, the model is guaranteed to meet MIL-STD-202 environmental test conditions that include temperature cycle, vibration, and shock.

Electrical Specifications

Switch Type	SP6T, Terminated
Actuator Type	Latching
Switching Sequence	Break Before Make
Actuator Options	Indicators, Self Cut Off, Reset
Polarity	Positive Common

Description	Min	Typ	Max	Units
Frequency Range	DC		40	GHz
Impedance		50		Ohms
Operating Voltage	20	24	32	Volts
Actuating Current @ 24 Volts		200		mA
Coil Resistance		120		Ohms
Third Order Intermodulation		-120		dBc
Input Power (CW)			5	Watts
Switching Time			15	ms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC - 6	6 - 12.4	12.4 - 18	18 - 26.5	26.5 - 40	GHz
VSWR, Max	1.2:1	1.35:1	1.45:1	1.7:1	1.9:1	
Insertion Loss, Max	0.39	0.486	0.57	0.7	0.9	dB
Isolation, Min	100	90	80	70	60	dB

Electrical Specification Notes:

Insertion Loss Repeatability at 25° is 0.05 dB



Features:

- DC to 40 GHz SP6T Switch
- Guaranteed Low Insertion loss Repeatability: 0.05 dB max over 5 Million Lifecycles
- Insertion Loss: 0.9 dB max
- Isolation: up to 60 dB min
- +24 Vdc Nominal Voltage
- Hot Switching: 1W CW max
- Latching Self Cutoff Actuator
- Position Indicators
- Guaranteed to meet MIL-STD-202 Environmental Conditions
- 2.92mm connectors
- HE10 receptacle with ribbon cable and HE10 connector
- -25°C to +75°C Operating Temperature
- 5 Million Lifecycles Minimum

Applications:

- Electronic Warfare
- Electronic Countermeasures
- Microwave Radio
- VSAT
- Radar
- Space Systems
- Test Instrumentation
- Research and Development
- Signal Monitoring Devices

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Mechanical Specifications

Size

Length	1.25 in [31.75 mm]
Width/Diameter	1.25 in [31.75 mm]
Height	0.5 in [12.7 mm]
Weight	0.595 lbs [269.89 g]
Body Material and Plating	Aluminum, Nickel
Package Type	Connectorized
Operating Life	5,000,000 Cycles

Connectors

RF Connector Type	2.92mm Female
RF Connector Contact Material & Plating	Beryllium Copper, Gold
RF Connector Body Material & Plating	Passivated Stainless Steel
Control Connector	HE 10

Environmental Specifications

Temperature

Operating Range	-25 to +75 deg C
Storage Range	-55 to +85 deg C

Humidity	MIL-STD-202, Method 106E, Condition E, 65°C, 95% RH, 10 days
Shock	MIL-STD-202, method 213B, Condition G, 50g, 6 ms, 1/2 Sine, Operating
Vibration	MIL-STD-202, Method 204D, Condition D, 10-2000 Hz, 10g, Operating
Altitude	MIL-STD-202-Method 105C, Condition B, 50,000 feet (15,240 meters)
Temperature Cycling	MIL-STD-202, Method 107D, Condition A, -55oC to +85oC, 10 cycles
EMI/RFI	MIL-STD-1344, Method 3008, or IEC 61726, 55 dB at 20 GHz
Magnetic Field	< 5x10-5 gauss at 1 meter
ESD Sensitivity	ESD Sensitive Material, Transport material in Approved ESD bags. Handle only in ESD Workstation.





Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data






SP6T Latching 0.05 dB Low Insertion Loss Repeatability DC to 40 GHz Terminated Relay Switch, Indicators, Self Cut Off, 5W, 24V, 2.92mm from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [SP6T Latching 0.05 dB Low Insertion Loss Repeatability DC to 40 GHz Terminated Relay Switch, Indicators, Self Cut Off, 5W, 24V, 2.92mm FMSW6332](https://www.fairviewmicrowave.com/sp6t-latching-electromechanical-relay-switch-indicators-reset-fmsw6332-p.aspx)

URL: <https://www.fairviewmicrowave.com/sp6t-latching-electromechanical-relay-switch-indicators-reset-fmsw6332-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



STANDARD TOLERANCES
DECIMAL

±0.02


*STANDARD TOLERANCES APPLY
ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC.
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

TITLE
SP6T Latching 0.05 dB Low Insertion Loss
Repeatability DC to 40 GHz Terminated Relay Switch,
Indicators, Self Cut Off, 5W, 24V, 2.92mm

DWG NO	FMSW6332	CAGE CODE	3FKR5
CAD FILE	031717	SHEET	SCALE N/A SIZE A 2233



STANDARD TOLERANCES
DECIMAL
±0.02

*STANDARD TOLERANCES APPLY
ONLY TO DIMENSIONS IN INCHES


FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

TITLE
SP6T Latching 0.05 dB Low Insertion Loss
Repeatability DC to 40 GHz Terminated Relay Switch,
Indicators, Self Cut Off, 5W, 24V, 2.92mm

DWG NO		FMSW6332		CAGE CODE		3FKR5	
CAD FILE	031717	SHEET		SCALE	N/A	SIZE	A 2233



ELECTRONIC POSITION INDICATORS

The electronic position indicators use photo-MOS transistors which are driven by the mechanical position of the RF paths moving elements. The circuitry consists of a common which can be connected to an output corresponding to selected RF path. If one or several RF paths are closed, the corresponding indicators are connected to the common. The photo-MOS transistors are configured for AC and/or DC operation. The electronic position indicators require the supply (20 to 32 VDC) to be connected to pin 1 and ground connected to pin 15.

STANDARD TOLERANCES

DECIMAL

±0.02

*STANDARD TOLERANCES APPLY
ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

TITLE

SP6T Latching 0.05 dB Low Insertion Loss
Repeatability DC to 40 GHz Terminated Relay Switch,
Indicators, Self Cut Off, 5W, 24V, 2.92mm

DWG NO

FMSW6332

CAGE CODE

3FKR5



CAD FILE 031717

SHEET

SCALE N/A

SIZE A

2233



Standard drive

- Connect pin 15 to ground.
- Connect pin 1 to supply (+20 VDC to +32 VDC)
- Select (close) desired RF path by applying Ground to the corresponding "drive" pin (Ex: apply Ground to pin 3 to close RF path 1).
- To select another path, ensure that all unwanted RF path "drive" pins are disconnected from Ground (to prevent multiple RF path engagement). Apply Ground to the "drive" pin which corresponds to the desired RF path.
- To open all RF paths, ensure that all RF path "drive" pins are disconnected from Ground. Complete the operation by applying Ground to pin 16.

Break-Before-Make

Open the undesired RF path. After 15 ms (minimum), close the new RF port.

Make-Before-Break

Ensure that the previously selected RF path "drive" is connected to Ground then close the new RF path.

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE SP6T Latching 0.05 dB Low Insertion Loss Repeatability DC to 40 GHz Terminated Relay Switch, Indicators, Self Cut Off, 5W, 24V, 2.92mm	DWG NO FMSW6332		CAGE CODE 3FKR5		
	CAD FILE 031717	SHEET	SCALE N/A	SIZE A	2233