



## 2.92mm 90 Degree Hybrid Coupler from 8 GHz to 43.5 GHz Rated to 20 Watts

The FMCP1149 is a high power 90 degree hybrid coupler that operates from 8 to 43.5 GHz and can handle 20 Watts (CW) with 12 dB isolation minimum and 1.8:1 VSWR maximum. The package interface uses 2.92mm Female connectors.

The FMCP1149 is part of Fairview Microwave's family of 90 degree hybrid couplers that offer excellent performance featuring high isolation, low insertion loss and VSWR while maintaining great amplitude/phase balance over the entire operating frequency range. They are available in both narrow and broad bandwidths and can be used in a wide variety of applications including signal sampling, phased array radar, and any application that requires even power distribution with a 90 degree difference in phase.

## **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	8		43.5	GHz
Impedance		50		Ohms
Phase Difference		90		Degrees
Coupling		3		dB
Insertion Loss		1.6	2	dB
Isolation	12	15		dB
VSWR		1.6:1	1.8:1	
Amplitude Balance		±0.5	±0.7	dB
Phase Balance		±6	±10	Degrees
Input Power (CW)			20	Watts
Input Power (Peak)			300	Watts



#### Features:

- 90° Phase Shift Between **Output Ports**
- High power handling of 20 Watts CW
- 8 to 43.5 GHz Frequency Range
- VSWR 1.6:1 Typical
- High Isolation of 12 dB Minimum
- Low 1.6 dB Insertion Loss Typical
- 2.92mm Female Connectors
- Stable performance over Operating Temperature Range

## **Applications:**

- Test and Measurement
- Commercial Communications
- SATCOM
- Military Communications
- · Wireless Communications

#### **Mechanical Specifications**

Size

Length Width Height Weight

1 in [25.4 mm] 0.43 in [10.92 mm] 0.63 in [16 mm] 0.15 lbs [68.04 g]

Configuration

RF Connector Type

2.92mm Female

# **Environmental Specifications**

**Temperature** 

Operating Range Storage Range

Humidity

Shock

Vibration

Altitude

-45 to +85 deg C -55 to +125 deg C

100% RH at 35°c, 95% RH

at 40°c 20G for 11msec half sine wave, 3 axis both

directions 25gRMS (15 degrees 2KHz) endurance, 1 hour

per axis

30,000 ft.

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com






### **Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**


Notes:

#### **Typical Performance Data**









2.92mm 90 Degree Hybrid Coupler from 8 GHz to 43.5 GHz Rated to 20 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 2.92mm 90 Degree Hybrid Coupler from 8 GHz to 43.5 GHz Rated to 20 Watts FMCP1149

URL: https://www.fairviewmicrowave.com/2.92mm-90-degree-hybrid-coupler-8-43.5-ghz-20-watts-fmcp1149-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





