

# SMA 180 Degree Hybrid Coupler from 2 GHz to 18 GHz Rated to 50 Watts

The FMCP1158 is a high power 180 degree hybrid coupler that operates from 2 to 18 GHz and can handle 50 Watts (CW) with 16 dB isolation minimum and 1.4:1 VSWR maximum. The package interface uses SMA Female connectors.

The FMCP1158 is part of Fairview Microwave's family of 180 degree hybrid couplers that offer excellent performance featuring high isolation, low insertion loss and VSWR while maintaining great amplitude/phase balance over the entire operating frequency range. They are available in both narrow and broad bandwidths and can be used in a wide variety of applications including signal sampling, phased array radar, and any application that requires even power distribution with a 180 degree difference in phase.

### **Electrical Specifications**

Description	Min	Тур	Мах	Units
Frequency Range	2		18	GHz
Impedance		50		Ohms
Phase Difference		180		Degrees
Coupling		3		dB
Insertion Loss		1.2	1.5	dB
Isolation	16	18		dB
VSWR		1.3:1	1.4:1	
Amplitude Balance		±0.8	±1	dB
Phase Balance		8	12	Degrees
Input Power (CW)			50	Watts
Input Power (Peak)			500	Watts

**Mechanical Specifications** 

<b>Size</b> Length Width Height Weight		3.23 in [82.04 mm] 0.89 in [22.61 mm] 0.43 in [10.92 mm] 0.25 lbs [113.4 g]	
<b>Configuration</b> RF Connector Type		SMA Female	
Environmental Specifi Temperature Operating Range	cations	-45 to +85 deg C	
Storage Range Humidity		-55 to +125 deg C 100% RH at 35°c, 95% RH	
Shock		at 40°c 20G for 11msec half sine wave, 3 axis both directions	
Vibration		25gRMS (15 degrees 2KHz) endurance, 1 hour per axis	
Altitude		30,000 ft.	

## FMCP1158 DATA SHEET



## Features:

- 180° Phase Shift Between
  Output Ports
- High power handling of 50 Watts CW
- 2 to 18 GHz Frequency Range
- VSWR 1.3:1 Typical
- High Isolation of 16 dB Minimum
- Low 1.2 dB Insertion Loss Typical
- SMA Female Connectors
- Stable performance over Operating Temperature Range

## **Applications:**

- Test and Measurement
- Commerical CommunicationsSATCOM
- Military Communications
- Wireless Communications

REV 1.0 Page 1 of 4 Copyright © 2020

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678

an INFINIT<sup>®</sup> brand



## Compliance Certifications (see product page for current document)

### **Plotted and Other Data**

Notes:


#### **Typical Performance Data**

dB Insertion Loss 0.0 -1.0 -2.0 -3.0 -4.0 -5.0 -6.0 -7.0 -8.0 -9.0 Including Coupling Loss -10.0 8.4 11.6 2.0 GHz 3.6 5.2 6.8 10.0 13.2 14.8 16.4 18.0 **VSWR** 3.0 2.8 2.6 2.4 2.2 2.0 1.8 1.6 1.4 1.2 1.0 2.0 GHz 3.6 10.0 11.6 13.2 14.8 18.0 5.2 6.8 8.4 16.4

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Fairview Microwave





SMA 180 Degree Hybrid Coupler from 2 GHz to 18 GHz Rated to 50 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: SMA 180 Degree Hybrid Coupler from 2 GHz to 18 GHz Rated to 50 Watts FMCP1158


URL: https://www.fairviewmicrowave.com/sma-180-degree-hybrid-coupler-2-18-ghz-50-watts-fmcp1158-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

an INFINIT<sup>®</sup> brand





301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689