

TNC Male (Plug) Termination (Load) 10 Watts to 12.4 GHz, Aluminum Body, 1.35:1 VSWR

Fairview Microwave's FMTR1140 is an RF termination (also called RF load or dummy load) that operates from DC to 12.4 GHz and handles up to 10 Watt (CW). Our TNC termination / load has a male gender. FMTR1140 TNC load termination offers 1.35:1 max VSWR.

RF load / terminations are indispensable components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can potentially damage the device or reduce the signal integrity. By using a terminator on an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These termination components are commonly used to terminate devices such as couplers, circulators, and switches. They are also widely used in measurement systems to ensure accurate results. Fairview Microwave offers a huge selection of RF, microwave and millimeter wave terminations up to 65 GHz with excellent performance over the entire operating range and power handling capabilities up to 800 Watt (CW).

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		12.4	GHz
Impedance		50		Ohms
VSWR			1.35:1	
Input Power (CW) Derated linearly to 1W at 125°C			10	Watts
Input Power (Peak) 5 μ s pulse, 1% Duty Cycle			1	kWatts

Mechanical Specifications

Size	
Length	2.39 in [60.71 mm]
Width	1.5 in [38.1 mm]
Height	1.5 in [38.1 mm]
Weight	0.19 lbs [86.18 g]

Configuration

Connector TNC Male

Material Specifications

Description	Material	Plating
Connector 1 Contact	Brass	Gold
Body	Black Anodized Aluminum	
Coupling Nut	Brass	Nickel
Housing	Black Anodized Aluminum	



Features:

- DC to 12.4 GHz Frequency Range
- 50 Ohm Impedance
- SMA Male Coaxial Interface
- Max VSWR 1.3:1
- Max Power 10 Watts (CW)

Applications:

- Instrumentation
- Precision Measurements
- Prototyping and Characterization
- Productions Systems
- WIFI 6E
- 5G Cellular Bands

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Environmental Specifications

Temperature

Operating Range -55 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

TNC Male (Plug) Termination (Load) 10 Watts to 12.4 GHz, Aluminum Body, 1.35:1 VSWR from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [TNC Male \(Plug\) Termination \(Load\) 10 Watts to 12.4 GHz, Aluminum Body, 1.35:1 VSWR FMTR1140](#)

URL: <https://www.fairviewmicrowave.com/rf-load-10-watts-12.4-ghz-tnc-male-fmtr1140-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

