



4 Way Power Divider N Interface from 375 MHz to 6 GHz Rated at 30 Watts

FMDV1050 is a passive 4 way RF Power Divider with 50 ohm N female connectors operating from 375 MHz to 6 GHz, with a max input power of 30 watts. The FMDV1050 has less than 30 dB Isolation, 2 dB Maximum Insertion loss and a Max VSWR of 1.5:1; along with a phase balance of ±4 degrees and an amplitude balance of ±0.3 dB. The RF Divider operates in a temperature range from -45°C to 85°C and are rated for Humidity, Shock, Vibration, and Altitude. Power dividers have many applications and so perform many valuable functions within the RF/ Microwave world. Examples are antenna beam forming, taps for cable distributed systems combining feeds to and from antennae.

Electrical Specifications

Design Number of Output Ports Wilkinson

Description	Min	Тур	Max	Units
Frequency Range	0.375		6	GHz
Impedance		50		Ohms
Input VSWR		1.4:1	1.5:1	
Insertion Loss			2	dB
Isolation	19	21		dB
Amplitude Balance		±0.25	±0.3	dB
Phase Balance		±3	±4	Degrees
Input Power (CW)			30	Watts
Reverse Power (CW)			2	Watts
Input Power (Peak)			300	Watts

Features:

- 375 MHz to 6 GHz
- 30 Watts Max Power
- ±4° Phase Balance
- 19 dB min Isolation
- 4 way N Type divider

Applications:

- Communications Systems
- Amplifier Systems
- · Amplifier Power Dividing
- Aerospace/Aviation
- Defense Applications

Mechanical Specifications

Size

Length

Width

Height

Weight

Finish

Housing Material and Plating

Configuration

Input Connector **Output Connectors**

Environmental Specifications Temperature

Operating Range

Storage Range

Humidity

3.94 in [100.08 mm]

0.79 in [20.07 mm] 3.62 in [91.95 mm]

0.9045 lbs [410.27

g]

Grav

Aluminum

N Female

N Female

-45 to +85 deg C

-55 to +125 deg C

100% RH at 35°C,

95% RH at 40°C

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Shock Vibration Altitude 20G for 11msec half sine wave, 3 axis both directions 25g RMS (15 degrees 2KHz) endurance, 1 hour per axis 30,000 ft. (Epoxy Sealed Controlled environment)

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

4 Way Power Divider N Interface from 375 MHz to 6 GHz Rated at 30 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 4 Way Power Divider N Interface from 375 MHz to 6 GHz Rated at 30 Watts FMDV1050

URL: https://www.fairviewmicrowave.com/4-way-power-divider-n-6-ghz-fmdv1050-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





