

# FMFD20001 **DATA SHEET**

## **SMA Frequency Divider Divide by 20 Prescaler** Module Operating from 200 MHz to 6 GHz

The FMFD20001 is a coaxial packaged Frequency Divider module that operates across a wide input frequency range from 200 MHz to 6 GHz and supports a divide ratio of 20. Output Frequency is 10 MHz to 300 MHz. Impressive broadband typical performance of this Prescaler includes output power of +2 dBm and SSB phase noise of -144 dBc/Hz at 100 kHz offset. This exceptional technical performance is achieved through the use of a hybrid MIC PCB solder assembly which is RoHS and REACH compliant. This frequency divider design requires +12 Vdc typical bias voltage, operates over maximum temperature range of -40°C to +85°C, and has an absolute maximum rating for input power of +13 dBm. The rugged and compact package supports SMA Female connectors, RFI and Ground Pins. For highly reliable operation, the model is guaranteed to meet MIL-STD-202 environmental test conditions for Humidity, Shock, Vibration, and Altitude.

### Electrical Specifications (TA= 25°C, Vd1 = 12 Vdc, Id1 = 95 mA)

Description	Min	Тур	Max	Units
Input Frequency (Sine Wave) 0.2			6	GHz
Output Frequency (Square Wave Output) 10			300	MHz
Output Power		2		dBm
Phase Noise @100kHz Offset		-144		dBc/Hz
Operating DC Voltage 1		12	15	V
Operating DC Current 1		95		mA

#### **Performance by Frequency**

F1	F2	F3	F4	F5	Units
0.2 to	1 1 to 6				GHz
12	12				dBm
-10	-12				dBm
	0.2 to	0.2 to 1 1 to 6 12 12			

#### **Mechanical Specifications**

Size

Length 1.25 in [31.75 mm] Width 1.25 in [31.75 mm] 0.563 in [14.3 mm] Height SMA Female **Output Connector** 

#### **Environmental Specifications**

**Temperature** 

Altitude

Operating Range -40 to +85 deg C Storage Range -55 to +125 deg C Humidity MIL-STD-202F, Method 103B, Condi-Shock MIL-STD-202F, Method 213B, Codition B Vibration MIL-STD-202F, Method 204D, Condi-

> tion B MIL-STD-202F, Method 105C, Condi-

tion B

#### Features:

- Wide Input Frequency Range: 200 MHz to 6 GHz
- Divide-by-20 Prescaler
- Output Frequency 10 MHz to 300 MHz
- Output Power: +2 dBm typical
- Low SSB Phase Noise: -144 dBc/ Hz @ 100 KHz offset typical
- RoHS & REACH Compliant Assembly
- Bias Voltage: +12 Vdc
- Operational Temperature Range: -40°C to +85°C
- Compact SMA Connectorized Package
- · Designed to meet MIL-STD-202 Test Conditions

### **Applications:**

- PLL Applications
- Test Instrumentation
- Countermeasures
- Point to Point Microwave Radio
- SATCOM
- MILCOM
- Base Stations

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






#### **Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:

#### **Typical Performance Data**



SMA Frequency Divider Divide by 20 Prescaler Module Operating from 200 MHz to 6 GHz from Fairview Microwave is instock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: SMA Frequency Divider Divide by 20 Prescaler Module Operating from 200 MHz to 6 GHz FMFD20001


URL: https://www.fairviewmicrowave.com/sma-frequency-divider-divide-20-prescaler-module-200-mhz-6-ghz-fmfd20001-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.











#### STANDARD TOLERANCES

.X ±0.2 .XX ±0.01 .XXX ±0.005

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

Fairview Microwave	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.					
an INFINIT <sup>®</sup> brand	3. DIMENSIONS ARE IN INCHES [mm].					
SMA Frequency Divider Divide by 20 Prescaler Module Operating from 200 MHz to 6 GHz	DWG NO FMFD20001			CAGE CODE 3FKR5		
	CAD FILE 04/26/18	SHEET 1 OF 1	SCAL	E N/A	SIZE A	7361