

Voltage Controlled Oscillator, 1070 MHz to 1210 MHz, Pout +1.5 dBm, Phase Noise of -109 dBc/Hz, 0.5V to 4.5V Tuning Range, SMA

The FMVC31020 is highly reliable low noise Voltage Controlled Oscillator (VCO) that operates across 1070 MHz to 1210 MHz with a tuning voltage range from 0.5V to 4.5V. Impressive typical performance includes generated output power of +1.5 dBm, 2nd Harmonic Suppression of -16 dBc, phase noise of -109 dBc/Hz @ 10 KHz offset, and tuning sensitivity of 37 MHz/V. The design incorporates internal voltage regulation and reverse DC protection, with a bias voltage range from +7V to +15V. The rugged and compact coaxial package assembly supports SMA female connectors, RFI and ground pins. The VCO has an operational temperature range of -40°C to +85°C and is designed to meet a variety of MIL-STD-202 test conditions including shock, vibration, altitude, and humidity.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	1.07		1.21	GHz
Tuning Voltage	0.5		4.5	Vdc
Supply Voltage (DC)	7	12	15	Vdc
Supply Current (DC)		20		mA
Phase Noise @10kHz Offset		-109		dBc/Hz
Output Power	-1	+1.5	+4	dBm
Tuning Sensitivity (Kvco)		37		MHz/V
Pulling (pk-pk)		1		MHz
Tuning Port Capacitance		100		pF
Load Impedance		50		Ohms
2nd Harmonics		-16		dBc

Mechanical Specifications

Size	
Length	1.25 in [31.75 mm]
Width	1.25 in [31.75 mm]
Height	0.563 in [14.3 mm]
Weight	0.4 lbs [181.44 g]
Design	Commercial
Connector Option	Standard
Output Connector	SMA Female

Environmental Specifications

Temperature	
Operating Range	-40 to +85 deg C
Storage Range	-55 to +100 deg C
Humidity	MIL-STD-202, Method 103B, Condition B
Shock	MIL-STD-202F, Method 213B, Condition B
Vibration	MIL-STD-202F, Method 204D, Condition B
Altitude	MIL-STD-202F, Method 105C, Condition B



Features:

- Voltage Controlled Oscillator
- 1070 MHz to 1210 MHz
- 0.5V to 4.5V Tuning Voltage
- Pout: +1.5 dBm
- Phase Noise: -109 dBc/Hz
- 2nd Harmonic Suppression: -16 dBc typ
- Tuning Sensitivity: 37 MHz/V
- +12 Volt DC Bias
- SMA Female Connectors
- -40°C to +85°C Operating Temperature
- 50 Ohm Design
- Internal Voltage Regulation
- Reverse DC Protection
- Rugged Package Design meets MIL-STD-202 Test Conditions

Applications:



- Phase Locked Loop
- Function Generators
- Frequency Synthesizers
- Receivers
- Electronic Jamming Equipment
- Local Oscillators
- Wireless Communications
- SATCOM
- Optical Communications
- Military Electronic Systems

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Typical Performance Data



Voltage Controlled Oscillator, 1070 MHz to 1210 MHz, Pout +1.5 dBm, Phase Noise of -109 dBc/Hz, 0.5V to 4.5V Tuning Range, SMA


Voltage Controlled Oscillator, 1070 MHz to 1210 MHz, Pout +1.5 dBm, Phase Noise of -109 dBc/Hz, 0.5V to 4.5V Tuning Range, SMA

Voltage Controlled Oscillator, 1070 MHz to 1210 MHz, Pout +1.5 dBm, Phase Noise of -109 dBc/Hz, 0.5V to 4.5V Tuning Range, SMA from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Voltage Controlled Oscillator, 1070 MHz to 1210 MHz, Pout +1.5 dBm, Phase Noise of -109 dBc/Hz, 0.5V to 4.5V Tuning Range, SMA FMVC31020](#)

URL: <https://www.fairviewmicrowave.com/vco-voltage-controlled-oscillator-1.21-ghz-fmvc31020-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



Voltage Controlled Oscillator, 1070 MHz to 1210 MHz,
Pout +1.5 dBm, Phase Noise of -109 dBc/Hz, 0.5V to
4.5V Tuning Range, SMA