



# Times Microwave LMR-100A-FR Low Loss Flexible Coax Cable Black FRPE Jacket Fire Rated

## **Times Microwave Systems Coax Cable Specification**

LMR-100-FR Fire Rated version of the 100 series Low Loss Coax from Times Microwave is part of the large product offering by Fairview Microwave of radio frequency coaxial cable types specifically stocked to be ready for same-day shipment. Fairview Microwave LMR-100-FR coax cable is manufactured in a flexible design and has a 50 Ohm impedance. This low loss and CMR riser rated 50 Ohm coax cable LMR-100-FR is constructed with a 0.110 inch diameter and Black FRPE jacket.

LMR-100-FR flexible 50 Ohm coax cable with FRPE jacket is rated for a 5.8 GHz maximum operating frequency. This 50 Ohm 0.110 inch diameter and low loss fire rated coax cable is built with an aluminum double shield count and RF shielding of 90 dB. Times Microwave LMR-100-FR FRPE coax is constructed with PE dielectric and a maximum operating temperature of 85 degrees C. Fairview Microwave's offering of LMR-100-FR coax cable provides specs for this wire on its RF coax cable LMR-100-FR datasheet.

LMR-100-FR cable is part of more than one million RF, microwave parts in stock at Fairview Microwave. This Times Microwave low loss flexible LMR-100-FR coax cable is ready to buy and can be shipped worldwide. Fairview Microwave also maintains a wide selection of other radio frequency coaxial cable types that ship same-day from our warehouse as with the rest of our other RF/microwave components.

\* LMR™ is a trademark of Times Microwave Systems.

### **Electrical Specifications**

Description	Min	Тур	Max	Units	
Frequency Range	DC		6	GHz	
Impedance		50		Ohms	
Velocity of Propagation		66		%	
Time Delay		1.54 [5.05]		ns/ft [ns/r	n]
Shielding Effectiveness	90			dB	
DWV (DC)			500	Vdc	
Jacket Spark			2,000	Vrms	
Inner Conductor DC Resist.			81	Ohms/100	0ft
Outer Conductor DC Resist.			9.5	Ohms/100	0ft
Nominal Capacitance		30.8		pF/ft	
		[101.05]		[pF/m]	
Nominal Inductance		0.077		uH/ft	
		[0.25]		[uH/m]	
Input Power (Peak)			600	Watts	

#### **Performance by Frequency Band**

Description	F1	F2	F3	F4	F5	Units
Frequency	50	150	220	450	900	MHz
Attenuation, Typ	5.1 16.73	8.9 29.2	10.9 35.76	15.8 51.84	22.8 74.8	dB/100ft dB/100m



## **Configuration:**

- Low Loss, Outdoor Flexible Cable
- 2 Shield(s)

#### Features:

- Max Operating Frequency of 5.8 GHz
- Phase Velocity 66% VoP
- Low Smoke, Zero Halogen FRPE Jacket
- CMR Riser Rated Coax
- Max Operating Temperature +85°C
- Min Install Bend Radius of 0.25 inches

## **Applications:**

- RF Test Systems
- In-Building Riser Runs
- Laboratory Applications
- Antenna Installs
- General Purpose RF Interconnect

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Power In (CW), Max	180	100	83	57	39	Watts
Description	F6	F7	F8	F9	F10	Units
Frequency	1.5	1.8	2	2.5	6	GHz
Attenuation, Typ	30.1 98.75	33.2 108.92	35.2 115.49	39.8 130.58	64.1 210.3	dB/100ft dB/100m
Power In (CW), Max	29	27	25	22	13	Watts

**Mechanical Specifications** 

Diameter Weight

Min. Bend Radius (Installation)
Min. Bend Radius (Repeated)

Bending Moment Tensile Strength Flat Plate Crush 0.11 in [2.79 mm] 0.009 lbs/ft [0.01 kg/m]

0.25 in [6.35 mm] 1 in [25.4 mm] 0.1 lbs-ft [0.14 N-m] 15 lbs [6.8 kg]

10 lbs/in [0.18 kg/mm]

**Construction Specifications** 

Description	Material and Plating	Diameter		
Inner Conductor	Copper, 1 Strands	0.018 in [0.46 mm]		
Conductor Type	Solid			
Dielectric	PE	0.06 in [1.52 mm]		
First Shield	Aluminum Tape	0.068 in [1.73 mm]		
Second Shield	Tinned Copper	0.083 in [2.11 mm]		
Jacket	FRPE, Black	0.11 in [2.79 mm]		

## **Environmental Specifications**

**Temperature**Operating Range

Operating Range -40 to +85 deg C
Installation Range -40 to +85 deg C
Storage Range -70 to +85 deg C

**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020 REV 1.1 Page 2 of 4





Times Microwave LMR-100A-FR Low Loss Flexible Coax Cable Black FRPE Jacket Fire Rated from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Times Microwave LMR-100A-FR Low Loss Flexible Coax Cable Black FRPE Jacket Fire Rated LMR-100A-FR-BULK

URL: https://www.fairviewmicrowave.com/lmr100fr-low-loss-flexible-coax-cable-frpe-jacket-lmr-100a-fr-bulk-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





