


## Times Microwave LMR-195 Low Loss Flexible Coax Cable Black PE Jacket



### LMR-195



## Times Microwave Systems Connector Specification

### Configuration

- Low Loss, Outdoor Flexible Cable
- 2 Shield(s)

### Features

- Max Operating Frequency of 8 GHz
- Low Loss Cable
- Phase Velocity 80% VoP

### Applications

- Laboratory Applications
- General Purpose RF Interconnect

### Description

LMR-195 coax cable from Fairview is only one of a large number of radio frequency twinaxial and coaxial cable types specifically stocked to be ready for quick shipment. Fairview Microwave LMR-195 coax cable is manufactured in a flexible design and has a 50 Ohm impedance. This low loss flexible 50 Ohm coax cable LMR-195 is constructed with a 0.195 inch diameter and PE jacket.

LMR-195 flexible 50 Ohm coax cable with PE jacket is rated for a 8 GHz maximum operating frequency. This 50 Ohm 0.195 inch diameter and low loss flexible coax cable is built with a shield count of 2 and RF shielding of 90 dB.

Fairview Microwave LMR-195 coax is constructed with PE (F) dielectric and a maximum operating temperature of 85 degrees C. Times Microwave LMR-195 coax cable specs for this wire properties can be found on its RF coax cable LMR-195 datasheet PDF specifications above.


LMR-195 cable is part of more than one million RF, microwave and millimeter wave parts in stock at Fairview. This Times Microwave low loss LMR-195 coax cable is ready to buy and can be shipped worldwide. Fairview also maintains a wide selection of other radio frequency twinaxial and coaxial cable types that ship same-day from our warehouse as with the rest of our other RF/microwave and millimeter wave components.

\* LMR™ is a trademark of Times Microwave Systems.

### Electrical Specifications

| Description                          | Minimum | Typical     | Maximum | Units        |
|--------------------------------------|---------|-------------|---------|--------------|
| Frequency Range                      | DC      |             | 8       | GHz          |
| Cutoff Frequency                     |         | 41          |         | GHz          |
| Impedance                            |         | 50          |         | Ohms         |
| Velocity of Propagation              |         | 80          |         | %            |
| Time Delay                           |         | 1.27 [4.17] |         | ns/ft [ns/m] |
| Shielding Effectiveness              | 90      |             |         | dB           |
| Dielectric Withstanding Voltage (DC) |         |             | 1,000   | Vdc          |
| Jacket Spark                         |         |             | 3,000   | Vrms         |
| Inner Conductor DC Resistance        |         |             | 7.6     | Ohms/1000ft  |

## Times Microwave LMR-195 Low Loss Flexible Coax Cable Black PE Jacket



### LMR-195

#### Electrical Specifications

| Description                   | Minimum | Typical      | Maximum | Units        |
|-------------------------------|---------|--------------|---------|--------------|
| Outer Conductor DC Resistance |         |              | 4.9     | Ohms/1000ft  |
| Nominal Capacitance           |         | 25.4 [83.33] |         | pF/ft [pF/m] |
| Nominal Inductance            |         | 0.064 [0.21] |         | uH/ft [uH/m] |
| Input Power (Peak)            |         |              | 2.5     | kWatts       |

#### Performance by Frequency Band

| Description           | F1  | F2    | F3    | F4    | F5    | Units    |
|-----------------------|-----|-------|-------|-------|-------|----------|
| Frequency             | 50  | 150   | 220   | 450   | 900   | MHz      |
| Attenuation, Typ      | 2.5 | 4.4   | 5.4   | 7.8   | 11.1  | dB/100ft |
|                       | 8.2 | 14.44 | 17.72 | 25.59 | 36.42 | dB/100m  |
| Input Power (CW), Max | 680 | 390   | 320   | 220   | 160   | Watts    |

| Description           | F6    | F7    | F8    | F9    | F10  | Units    |
|-----------------------|-------|-------|-------|-------|------|----------|
| Frequency             | 1.5   | 1.8   | 2     | 2.5   | 5.8  | GHz      |
| Attenuation, Typ      | 14.5  | 16    | 16.9  | 19    | 29.9 | dB/100ft |
|                       | 47.57 | 52.49 | 55.45 | 62.34 | 98.1 | dB/100m  |
| Input Power (CW), Max | 120   | 110   | 100   | 90    | 60   | Watts    |


#### Mechanical Specifications

|                                 |                          |
|---------------------------------|--------------------------|
| Diameter                        | 0.195 in [4.95 mm]       |
| Weight                          | 0.022 lbs/ft [0.03 kg/m] |
| Min. Bend Radius (Installation) | 0.5 in [12.7 mm]         |
| Min. Bend Radius (Repeated)     | 2 in [50.8 mm]           |
| Bending Moment                  | 0.2 lbs-ft [0.27 N-m]    |
| Tensile Strength                | 40 lbs [18.14 kg]        |
| Flat Plate Crush                | 15 lbs/in [0.27 kg/mm]   |

#### Construction Specifications

| Description     | Material and Plating | Diameter           |
|-----------------|----------------------|--------------------|
| Inner Conductor | Copper, 1 Strand     | 0.037 in [0.94 mm] |
| Conductor Type  | Solid                |                    |
| Dielectric      | PE (F)               | 0.11 in [2.79 mm]  |
| First Shield    | Aluminum Tape        |                    |
| Second Shield   | Tinned Copper Braid  |                    |
| Jacket          | PE, Black            | 0.195 in [4.95 mm] |

## Times Microwave LMR-195 Low Loss Flexible Coax Cable Black PE Jacket



### LMR-195

---

#### Environmental Specifications

##### Temperature

|                 |                 |
|-----------------|-----------------|
| Operating Range | -40 to 85 deg C |
| Storage Range   | -70 to 85 deg C |

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

Times Microwave LMR-195 Low Loss Flexible Coax Cable Black PE Jacket from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Times Microwave LMR-195 Low Loss Flexible Coax Cable Black PE Jacket LMR-195](#)

URL: <https://www.fairviewmicrowave.com/lmr195-low-loss-flexible-coax-cable-pe-jacket-lmr-195-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

LMR-195 CAD Drawing
Times Microwave LMR-195 Low Loss Flexible Coax Cable Black PE Jacket

