



# Transfer Electromechanical Relay Latching Switch DC to 40 GHz, 2M cycles, 2.92mm, 5 Watts, 12V, Self Cut Off, TTL, Diodes, Solder Pins

The FMSW6484 is a Transfer electromechanical relay switch that operates across a wide frequency range of DC to 40 GHz and can handle up to 5W of average power in a break before make condition. The 50 Ohm design is rated for 2 million lifecycles and features a Latching Self Cut-Off Actuator that magnetically latches in place after the control voltage is removed. For power sensitive applications, this is the best actuator option. Additional features include TTL control logic, and suppression diodes which limit voltage spikes or reverse current. Impressive typical performance includes 0.4 dB insertion loss and isolation greater than 85 dB. This switch requires +12Vdc bias voltage and operates over a temperature range of -25°C to +65°C. The rugged and compact package assembly supports 2.92mm female connectors and solder terminal pins for DC command control functions. And for highly reliable operation, the model is guaranteed to meet MIL-STD-202 environmental test conditions for shock and random vibration.

# **Electrical Specifications** (TA = +25°C, DC Voltage = +12 Vdc)

Switch Type Transfer
Actuator Type Latching

Actuator Options Self Cut Off, TTL Logic TTL Control on: 2.4 to 5.5 Volts

off: 0 to 0.8 Volts

Description	Min	Тур	Max	Units
Frequency Range	DC		40	GHz
Operating Voltage		+12		Volts
Actuating Current @ +12 \		300	mA	
VSWR		1.4:1	1.8:1	
Insertion Loss		0.4	1	dB
Isolation	50	85		dB
Input Power (CW) (at 40 GHz)			5	Watts

### **Performance by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC - 6	6 - 12.4	12.4 - 26.5	26.5 - 40		GHz
VSWR, Max	1.2:1	1.3:1	1.4:1	1.8:1		
Insertion Loss, Max	0.2	0.4	0.7	1		dB
Isolation, Min	85	80	65	50		dB

# **Mechanical Specifications**

#### Size

 Length
 2 in [50.8 mm]

 Width/Diameter
 2.16 in [54.86 mm]

 Height
 1.26 in [32 mm]

 Weight
 0.4 lbs [181.44 g]



#### **Features:**

- Transfer Electromechanical Relay Switch
- DC to 40 GHz Frequency Range
- Latching Self Cut-Off Actuator
- TTL Logic Control
- Suppression Diodes
- 2M Lifecycle Rating
- Insertion Loss 0.4 dB typ
- Isolation > 85 dB typ
- VSWR as low as 1.2:1 max
- 2.92mm Female Connectors
- +12 Volt DC Bias
- Solder Terminal Pins for DC Command Control
- -25°C to +65°C Operating Temperature
- Up to 5 Watt Average Power Handling
- 50 Ohm Design
- Hot Switching Capability
  - Consult Factory
- S-Parameter Data available upon request
- Rugged Design meets Mil-STD-202 Test Conditions

# **Applications:**

- Aerospace & Defense
- Test & Measurement
- Microwave Radio Systems
- Military & Commercial Communication Systems
- Research & Development
- SATCOM
- Wireless Communications
- Enterprise
- IoT

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





**Connectors** 

RF Connector Type 2.92mm Female

# **Environmental Specifications**

**Temperature** 

Operating Range -25 to +65 deg C Storage Range -55 to +100 deg C


Shock MIL-STD-202 Method 213, Condition D, 500G (non oper)
Vibration MIL-STD-202 Method 204, Condition D, 10G RMS (non oper)


## **Compliance Certifications** (see product page for current document)

# **Plotted and Other Data**

Notes:

## **Typical Performance Data**






301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020 REV 1 Page 2 of 7












## Power Handling vs. Frequency








Transfer Electromechanical Relay Latching Switch DC to 40 GHz, 2M cycles, 2.92mm, 5 Watts, 12V, Self Cut Off, TTL, Diodes, Solder Pins from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Transfer Electromechanical Relay Latching Switch DC to 40 GHz, 2M cycles, 2.92mm, 5 Watts, 12V, Self Cut Off, TTL, Diodes, Solder Pins FMSW6484

URL: https://www.fairviewmicrowave.com/transfer-latching-40-ghz-electro-mechanical-relay-switch-ttl-5w-12v-2.92mm-fmsw6484-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





