

## 5 dB Fixed Attenuator N Male (Plug) to N Female (Jack) Up to 6 GHz Rated to 2 Watts, Brass Tri-Metal Body, 1.25 VSWR

### SA6021-05



#### Features

- Bidirectional
- DC to 6 GHz Frequency Range
- Attenuation  $5 \pm 0.75$  dB
- Max Power 2 Watts (CW)
- VSWR < 1.25:1

#### Applications

- Instrumentation
- Precision measurements
- Prototyping and characterization
- Production systems

#### Description

Fairview Microwave carries a broad selection of fixed attenuators with a wide range of attenuation levels, frequency ranges, and power dissipation ranges. Also known as RF pads, RF microwave attenuators lower the amplitude of a signal (or attenuate) a known amount. These attenuator pads can be used in a wide variety of applications including reducing a signal level to protect measurement equipment or other circuitry, extending the range of power meters and amplifiers, and impedance matching circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Fairview Microwave carries one of the largest in-stock varieties and ships them same day. The SA6021-05 is a 5 dB Fixed Attenuator that operates from DC to 6 GHz and is rated to 2 Watts. The versatile coaxial package uses type N male to type N female connectors.

#### Electrical Specifications

| Description                      | Minimum | Typical | Maximum | Units |
|----------------------------------|---------|---------|---------|-------|
| Frequency Range                  | DC      |         | 6       | GHz   |
| Impedance                        |         | 50      |         | Ohms  |
| Nominal Attenuation              |         | 5       |         | dB    |
| Attenuation Accuracy             |         | 0.75    |         | dB    |
| VSWR                             |         |         | 1.25:1  |       |
| Input Power, CW                  |         |         | 2       | Watts |
| derated linearly to 0.2W @ 125°C |         |         |         |       |

#### Specifications by Frequency

| Description     | F1      | F2     | F3 | F4 | F5 | Units |
|-----------------|---------|--------|----|----|----|-------|
| Frequency Range | DC to 3 | 3 to 6 |    |    |    | GHz   |
| VSWR, Max       | 1.15:1  | 1.25:1 |    |    |    |       |

#### Mechanical Specifications

##### Size

|                           |                     |
|---------------------------|---------------------|
| Length                    | 1.61 in [40.89 mm]  |
| Width/Diameter            | 0.79 in [20.07 mm]  |
| Height                    | 0 in [0 mm]         |
| Weight                    | 0.107 lbs [48.53 g] |
| Body Material and Plating | Brass, Tri-Metal    |

5 dB Fixed Attenuator N Male (Plug) to N Female (Jack) Up to 6 GHz Rated to 2 Watts, Brass Tri-Metal Body, 1.25 VSWR



SA6021-05

|               |                      |
|---------------|----------------------|
| Configuration |                      |
| Design        | Fixed, Bidirectional |
| Package Style | Connectorized        |

Connectors

| Description                       | Connector 1           | Connector 2           |
|-----------------------------------|-----------------------|-----------------------|
| Type                              | N Male                | N Female              |
| Contact Material and Plating      | Phosphor Bronze, Gold | Phosphor Bronze, Gold |
| Contact Plating Specification     | 30 μ-inch             | 30 μ-inch             |
| Dielectric Type                   | Teflon                | Teflon                |
| Coupling Nut Material and Plating | Brass, Tri-Metal      |                       |
| Body Material and Plating         | Brass, Tri-Metal      | Brass, Tri-Metal      |

Environmental Specifications

|                 |                   |
|-----------------|-------------------|
| Temperature     |                   |
| Operating Range | -55 to +125 deg C |
| Storage Range   | -55 to +125 deg C |

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data



Notes:

5 dB Fixed Attenuator N Male (Plug) to N Female (Jack) Up to 6 GHz Rated to 2 Watts, Brass Tri-Metal Body, 1.25 VSWR



## SA6021-05

### Typical Performance Data



5 dB Fixed Attenuator N Male (Plug) to N Female (Jack) Up to  
6 GHz Rated to 2 Watts, Brass Tri-Metal Body, 1.25 VSWR



## SA6021-05

5 dB Fixed Attenuator N Male (Plug) to N Female (Jack) Up to 6 GHz Rated to 2 Watts, Brass Tri-Metal Body, 1.25 VSWR from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [5 dB Fixed Attenuator N Male \(Plug\) to N Female \(Jack\) Up to 6 GHz Rated to 2 Watts, Brass Tri-Metal Body, 1.25 VSWR SA6021-05](https://www.fairviewmicrowave.com/5db-fixed-attenuator-n-male-n-female-2-watts-sa6021-05-p.aspx)

URL: <https://www.fairviewmicrowave.com/5db-fixed-attenuator-n-male-n-female-2-watts-sa6021-05-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.