

FMTR1108 DATA SHEET

RF Load 1 Watts to 40 GHz 2.92mm Female

RF termination (also called RF load or dummy load) FMTR1108 from Fairview Microwave operates from DC to 40 GHz and handles up to 1 Watt (CW). This 2.92mm termination (or load) is a 50 Ohm impedance and has a Female gender. PFMTR1108 50 Ohm 2.92mm load termination offers 1.15:1 max VSWR.

RF terminations / loads are critical passive components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can reduce the signal integrity can potentially damage the device. By terminating an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These radio frequency termination components are commonly used to terminate devices such as couplers, circulators, and switches. Loads / terminations are also widely used in measurement systems to ensure accurate results. Fairview Microwave offers a large selection of in-stock RF, microwave and millimeter wave terminations up to 65 GHz with great performance over the entire operating range and with power handling capabilities up to 800 Watts (CW).

Electrical Specifications

Min	Тур	Мах	Units
DC		40	GHz
	50		Ohms
		1.15:1	
		1	Watt
		DC	DC 40

Mechanical Specifications

Size Length Width	0.76 in [19.3 mm] 0.31 in [7.87 mm]
Configuration Connector Hex Size Durability	2.92mm Female 5/16 inch 500 Cycles

Material Specifications

Material	Plating
Beryllium Copper	Gold
Passivated Stainless Steel	
Passivated Stainless Steel	
	Beryllium Copper Passivated Stainless Steel

Mechanical Specification Notes: Interface: MIL-STD-348B

Environmental Specifications Temperature

Operating Range



Features:

- 50 Ohm RF Load
- DC to 40 GHz Frequency Range
- VSWR 1.15:1 Max
- Max Power 1 Watt (CW)
- 2.92mm Female Coaxial Interface

Applications:

- Wireless
- SatCom
- Radar Systems
- Test and Measurement
- Commercial and Military
 Communication

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Humidity Thermal Shock Salt Spray MIL-STD-202, Method 106 MIL-STD-202, Method 107, Condition B MIL-STD-202, Method 101, Condition B

Compliance Certifications (see product page for current document)

Plotted and Other Data


Notes:

RF Load 1 Watts to 40 GHz 2.92mm Female from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: RF Load 1 Watts to 40 GHz 2.92mm Female FMTR1108


URL: https://www.fairviewmicrowave.com/rf-load-1-watts-40-ghz-2.92mm-female-fmtr1108-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.









301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689