

## N Male (Plug) Termination (Load) 2 Watts DC to 12 GHz With Chain, Brass Body, 1.2:1 VSWR

Fairview Microwave's FMTR1142C is an RF termination (also called RF load or dummy load) that operates from DC to 12 GHz and handles up to 2 Watt (CW). Our N termination / load has a male gender. FMTR1142C N load termination offers 1.2:1 max VSWR.

RF load / terminations are indispensable components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can potentially damage the device or reduce the signal integrity. By using a terminator on an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These termination components are commonly used to terminate devices such as couplers, circulators, and switches. They are also widely used in measurement systems to ensure accurate results. Fairview Microwave offers a huge selection of RF, microwave and millimeter wave terminations up to 65 GHz with excellent performance over the entire operating range and power handling capabilities up to 800 Watt (CW).



### Features:

- DC to 12 GHz Frequency Range
- 50 Ohm Impedance
- N Male Coaxial Interface
- Max VSWR 1.2:1
- Max Power 2 Watts (CW)
- Includes Beaded Chain

### Applications:

- WIFI 6E
- 5G Cellular bands
- SatCom
- Radar Systems
- Test and Measurement
- Commercial and Military Communication

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		12	GHz
Impedance		50		Ohms
VSWR			1.2:1	
Input Power (CW)			2	Watts
Derated linearly to 1W at +165°C				
DWV (DC)			2,500	Vdc
Operating Voltage (DC)			1,000	Vdc

### Mechanical Specifications

<b>Size</b>	
Length	0.866 in [22 mm]
Width	0.827 in [21.01 mm]
Height	0.827 in [21.01 mm]
Weight	0.09 lbs [40.82 g]
Package Type	Connectorized

### Configuration

Connector	N Male
-----------	--------

### Material Specifications

Description	Material	Plating
Connector 1 Contact	Beryllium Copper	Gold
Insulation	Teflon	
Body	Brass	Copper-Tin-Zinc Alloy
Coupling Nut	Brass	Copper-Tin-Zinc Alloy
Chain	Brass	Copper-Tin-Zinc Alloy

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

### Environmental Specifications

#### Temperature

Operating Range	-55 to +165 deg C
Humidity	MIL-STD-202, Method 106
Thermal Shock	MIL-STD-202, Method 107, Condition B
Salt Spray	MIL-STD-202, Method 101, Condition B

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

N Male (Plug) Termination (Load) 2 Watts DC to 12 GHz With Chain, Brass Body, 1.2:1 VSWR from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [N Male \(Plug\) Termination \(Load\) 2 Watts DC to 12 GHz With Chain, Brass Body, 1.2:1 VSWR FMTR1142C](#)

URL: <https://www.fairviewmicrowave.com/2-watts-12-ghz-n-male-fmtr1142c-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

