

SMA/M-SMA/MRA FLEXIBLE CABLES 3 GHZ RG174

SCB15179-XX


SPECIFICATIONS

CABLE ASSEMBLY:
VSWR: 1.2:1 @ < 3GHZ TYPICAL


RAW CABLE: RG174
TYPICAL LOSS (EXCLUDING CONNECTORS)
@0.1GHz 0.08 DB/FT
@0.5GHz 0.19 DB/FT
@1GHz 0.27 DB/FT
@2GHz 0.39 DB/FT
@3GHz 0.49 DB/FT

CONNECTORS:
BRASS SMA torque 5-in-lbs
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

TEMPERATURE: -55° to +110°C



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/M-SMA/MRA FLEXIBLE CABLES 3 GHZ RG174

SIZE

A

CAGE CODE

3FKR5

DWG NO

SCB15179-XX

REV

--

SCALE

SHEET