

N-TNC 18GHZ FLANGE ADAPTERS

SM4148

SPECIFICATIONS

ELECTRICAL



FREQUENCY: 0-18 GHZ
IMPEDANCE: 50 OHMS
VSWR: 1.15:1 MAX

MECHANICAL

MATERIALS BODY: PASSIVATED STAINLESS STEEL
MATERIALS CONTACT: BeCu
CONTACT PLATING: Au MIL-G-45204
INSULATOR: TEFLON
INTERFACE: MIL-STD-883A
DURABILITY: 500 CYCLES MIN

OPERATING TEMPERATURE: -55 to 100°C

ROHS COMPLIANT
MEASUREMENTS BELOW ARE TYPICAL



FAIRVIEW MICROWAVE

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

N-TNC 18GHZ FLANGE ADAPTERS

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SM4148	C
SCALE		SHEET	

ALL DIMENSIONS IN inches(MM) Typical