



# Brass WR-112 Waveguide Pressure Window with UG-51/U and UG-51/U-Grooved Flanges

Waveguide pressure windows are used to isolate pressurized components from non-pressurized components within a waveguide system. They can also provide protection against contaminants (debris, moisture and dust) from entering the waveguide system and degrading its RF performance. The FMWGP1007 is a WR-112 waveguide pressure windows that operates in the frequency range of 6.57 GHz to 9.9 GHz. This WR-112 waveguide termination has a Max VSWR of 1.25:1. This waveguide pressure window is made of annealed copper and incorporates UG-51/U and UG-51/U-Grooved flange interface. In addition to waveguide pressure window product line, Fairview Microwave also offers a wide range of waveguide products which are available in stock and ready for same-day shipment.



Description	Min	Тур	Max	Units
Frequency Range	6.57		9.99	GHz
VSWR			1.25:1	
Insertion Loss			0.2	dB
Input Power			1,000	kWatts

## **Mechanical Specifications**

Copper Brass
Passivation
1.881 in [47.78 mm]
1.881 in [47.78 mm]
0.787 in [19.99 mm]
0.33 lbs [149.69 g]

#### **Compliance Certifications** (see product page for current document)

Brass WR-112 Waveguide Pressure Window with UG-51/U and UG-51/U-Grooved Flanges from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Brass WR-112 Waveguide Pressure Window with UG-51/U and UG-51/U-Grooved Flanges FMWGP1007

URL: https://www.fairviewmicrowave.com/fmwgp1007-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



## **Features:**

- WR-112 Waveguide
- Operating Frequency Range from 6.57 GHz to 9.99 GHz
- UG-51/U and UG-51/U-Grooved Flanges
- 1.25:1 Max VSWR
- 1000 Watts (CW) Max Power Handling
- Insertion loss: 0.2 dB Max
- Thickness: 0.79 inches
- PTFE window material
- Pressure Handling Capability: 29 PSI Max

# **Applications:**

- Radar Systems
- Military and Space
- Wireless Radio Systems
- Communication Systems
- R&D Labs
- Microwave Radio Systems

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





