

RA N Male (Plug) to N Female (Jack) Adapter, Nickel Plated Brass Body, High Temp, 1.3 VSWR

RA type N male to type N female adapter part number SM4529 from Fairview Microwave is in-stock and ships same day. This Fairview type N to type N adapter has a male to female gender configuration. SM4529 type N male to type N female adapter operates to 11 GHz. The Fairview Microwave RF adapter provides good VSWR of 1.3:1 maximum. This right angle type N adapter allows for easier connections in tight spaces.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		11	GHz
VSWR			1.3:1	
Operating Voltage (AC)			1,000	Vrms

Electrical Specification Notes:
Values at 25°C, sea level.

Mechanical Specifications

Size	
Length	1.441 in [36.6 mm]
Width	1.268 in [32.21 mm]
Height	1.371 in [34.82 mm]
Weight	0.157 lbs [71.21 g]

Description	Connector 1	Connector 2
Type	N Male	N Female
Polarity	Standard	Standard
Interface Specification	MIL-STD-348A	MIL-STD-348A



Configuration:

- N Male Connector 1
- N Female Connector 2
- 50 Ohm
- Right Angle Body Geometry

Features:

- VSWR of 1.3:1 max up to 11 GHz
- Type N interface meets MIL-STD-348A
- 30µ in. minimum contact plating
- Gold Plated Brass Contact

Applications:

- General Purpose Test

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Material Specifications

Description	Connector 1	Connector 2
Type	N Male	N Female
Contact Material	Brass	Brass
Contact Plating	Gold	Gold
Contact Plating Spec.	30μ in. minimum	30μ in. minimum
Insulation Material	PTFE	PTFE
Outer Contact Material		Brass
Outer Contact Plating		Nickel
Outer Conductor Contact Spec.		100 μin minimum
Body Material	Brass	
Body Plating	Nickel	
Body Plating Spec.	100 μin minimum	
Gasket Material	Silicone	
Coupling Nut Material	Brass	
Coupling Nut Plating	Nickel	
Coupling Nut Plating Spec.	100 μin minimum	

Environmental Specifications

Temperature


Operating Range -65 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data




RA N Male (Plug) to N Female (Jack) Adapter, Nickel Plated Brass Body, High Temp, 1.3 VSWR from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [RA N Male \(Plug\) to N Female \(Jack\) Adapter, Nickel Plated Brass Body, High Temp, 1.3 VSWR SM4529](#)

URL: <https://www.fairviewmicrowave.com/ra-n-male-n-female-adapter-sm4529-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





STANDARD TOLERANCES	
.X	±0.2
.XX	±0.1
.XXX	±0.05

*STANDARD TOLERANCES APPLY
ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

TITLE

RA N Male (Plug) to N Female (Jack) Adapter, Nickel
Plated Brass Body, High Temp, 1.3 VSWR

DWG NO

SM4529

CAGE CODE

3FKR5

CAD FILE

121715

SHEET

SCALE N/A

SIZE A

150