

ADAPTER 7-16/M to TNC/F

SM4666

SPECIFICATIONS

ELECTRICAL

FREQUENCY: 0-8 GHz

IMPEDANCE: 50 OHMS

VSWR: 1.10 MAX @ DC-3 GHz

1.25 MAX @ 3-6 GHz

1.35 MAX @ 6-8 GHz

ENVIRONMENTAL

-40°C to +120 °C

MATERIALS

DIN(M) BODY: TRIPLATED BRASS

TNC(F) BODY: PASS. STAINLESS STEEL



CENTER CONTACTS: Au PLATED BeCu

O RING: SILICON RUBBER

INSULATOR: PTFE

INTERFACE: MIL-STD-883

ROHS COMPLIANT



ALL DIMENSIONS IN inches(mm) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

ADAPTER 7-16/M to TNC/F

SIZE

A

CAGE CODE

3FKR5

DWG NO

SM4666

REV

--

SCALE

SHEET