



# Times Microwave LMR-100A-UF Low Loss Flexible Coax Cable Black TPE Jacket Ultra Flex

## **Times Microwave Systems Coax Cable Specification**

LMR-100-UF Ultra Flex version of the 100 series Low Loss Coax from Times Microwave is part of the large product offering by Fairview Microwave of radio frequency coaxial cable types specifically stocked to be ready for same-day shipment. Fairview Microwave LMR-100-UF coax cable is manufactured in an ultra flexible design and has a 50 Ohm impedance. This low loss and ultra flexible 50 Ohm coax cable LMR-100-UF is constructed with a 0.110 inch diameter and Black TPE jacket.

LMR-100-UF flexible 50 Ohm coax cable with TPE jacket is rated for a 5.8 GHz maximum operating frequency. This 50 Ohm 0.110 inch diameter and low loss ultra flexible coax cable is built with an aluminum double shield count and RF shielding of 90 dB. Times Microwave LMR-100-UF TPE coax is constructed with PE dielectric and a maximum operating temperature of 85 degrees C. Fairview Microwave's offering of LMR-100-UF coax cable provides specs for this wire on its RF coax cable LMR-100-UF datasheet.

LMR-100-UF cable is part of more than one million RF, microwave parts in stock at Fairview Microwave. This Times Microwave low loss ultra flexible LMR-100-UF coax cable is ready to buy and can be shipped worldwide. Fairview Microwave also maintains a wide selection of other radio frequency coaxial cable types that ship same-day from our warehouse as with the rest of our other RF/microwave components.

\* LMR™ is a trademark of Times Microwave Systems.

#### **Electrical Specifications**

Description	Min	Тур	Max	Units		
Frequency Range	DC		6	GHz		
Impedance		50		Ohms		
Velocity of Propagation		66		%		
Time Delay		1.54 [5.05]		ns/ft [ns/m]		
Shielding Effectiveness	90			dB		
DWV (DC)			500	Vdc		
Jacket Spark			2,000	Vrms		
Inner Conductor DC Res	ist.		81	Ohms/1000ft		
Outer Conductor DC Res	ist.	9.5 Ohms/1000				
Nominal Capacitance		30.8	pF/ft			
		[101.05]		[pF/m]		
Nominal Inductance		0.077	uH/ft			
		[0.25]		[uH/m]		
Input Power (Peak)			Watts			

#### **Performance by Frequency Band**

Description	F1	F2	F3	F4	F5	Units	
Frequency	50	150	220	450	900	MHz	
Attenuation, Typ	5.1 16.73	8.9 29.2	10.9 35.76	15.8 51.84	22.8 74.8	dB/100ft dB/100m	



## **Configuration:**

- Low Loss, Outdoor Flexible Cable
- 2 Shield(s)

#### Features:

- Max Operating Frequency of 5.8 GHz
- Phase Velocity 66% VoP
- Stranded Center Conductor Resulting in an Ultra Flexible Coax
- Max Operating Temperature +85°C
- TPE Jacket
- Min Install Bend Radius of 0.25 inches

## **Applications:**

- Laboratory Applications
- General Purpose RF Interconnect
- RF Test Systems Requiring Highly Flexible Coax
- Antenna Installs

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Power In (CW), Max	180	100	83	57	39	Watts
Description	F6	F7	F8	F9	F10	Units
Frequency	1.5	1.8	2	2.5	6	GHz
Attenuation, Typ	30.1 98.75	33.2 108.92	35.2 115.49	39.8 130.58	64.1 210.3	dB/100ft dB/100m
Power In (CW), Max	29	27	25	22	13	Watts

## **Mechanical Specifications**

Diameter Weight

Min. Bend Radius (Installation) Min. Bend Radius (Repeated)

Bending Moment Tensile Strength Flat Plate Crush 0.11 in [2.79 mm] 0.008 lbs/ft [0.01 kg/m]

0.25 in [6.35 mm] 1 in [25.4 mm] 0.1 lbs-ft [0.14 N-m] 15 lbs [6.8 kg]

10 lbs/in [0.18 kg/mm]

### **Construction Specifications**

Description	<b>Material and Plating</b>	Diameter
Inner Conductor	Copper, 1 Strands	0.018 in [0.46 mm]
Conductor Type	Stranded	
Dielectric	PE	0.06 in [1.52 mm]
First Shield	Aluminum Tape	0.068 in [1.73 mm]
Second Shield	Tinned Copper	0.083 in [2.11 mm]
Jacket	TPE, Black	0.11 in [2.79 mm]

# **Environmental Specifications**

**Temperature** 

Operating Range -40 to +85 deg C Installation Range -40 to +85 deg C Storage Range -70 to +85 deg C

**Compliance Certifications** (see product page for current document)

**Plotted and Other Data** 

Notes:

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020 REV 2.1 Page 2 of 4





Times Microwave LMR-100A-UF Low Loss Flexible Coax Cable Black TPE Jacket Ultra Flex from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Times Microwave LMR-100A-UF Low Loss Flexible Coax Cable Black TPE Jacket Ultra Flex LMR-100A-UF-BULK

URL: https://www.fairviewmicrowave.com/lmr-100a-uf-low-loss-flexible-coax-cable-tpe-jacket-lmr-100a-uf-bulk-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order

to implem	ent improven	nents. Fairview	Microw	ave reserv	es the righ	nt to mak	ke such	changes	as req	uired. l	Jnless (	otherwise
stated, al	l specification	s are nominal.	Fairvie	w Microwa	ve does n	ot make	any re	presentat	ion or	warrant	y rega	rding the
suitability	of the part d	lescribed hereir	for any	particular	purpose,	and Fair	rview M	licrowave	does	not assu	ıme an	y liability
arising ou	t of the use o	of any part or do	cument	ation.								

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





