an INFINIT© brand

# Times Microwave LMR-LW195 Low Loss Flexible Coax Cable Black PE Jacket Light Weight

## **Times Microwave Systems Coax Cable Specification**

LMR-LW195 Light weight version of the 195 series Low Loss Coax from Times Microwave is part of the large product offering by Fairview Microwave of radio frequency coaxial cable types specifically stocked to be ready for same-day shipment. Fairview Microwave LMR-LW195 coax cable is manufactured in a flexible design and has a 50 Ohm impedance. This low loss and light weight flexible 50 Ohm coax cable LMR-LW195 is constructed with a 0.195 inch diameter and Black PE jacket.

LMR-LW195 flexible 50 Ohm coax cable with PE jacket is rated for a 8 GHz maximum operating frequency. This 50 Ohm 0.195 inch diameter and low loss flexible coax cable is built with an aluminum double shield count and RF shielding of 90 dB. Times Microwave LMR-LW195 PE coax is constructed with Foam PE dielectric and a maximum operating temperature of 85 degrees C. Fairview Microwave's offering of LMR-LW195 coax cable provides specs for this wire on its RF coax cable LMR-LW195 datasheet.

LMR-LW195 cable is part of more than one million RF, microwave parts in stock at Fairview Microwave. This Times Microwave low loss and light weight LMR-LW195 coax cable is ready to buy and can be shipped worldwide. Fairview Microwave also maintains a wide selection of other radio frequency coaxial cable types that ship sameday from our warehouse as with the rest of our other RF/microwave components.

\* LMR<sup>™</sup> is a trademark of Times Microwave Systems.

#### **Electrical Specifications**

_					
Description	Min	Min Typ		Units	
Frequency Range	DC		8	GHz	
Impedance		50		Ohms	
Velocity of Propagation		80		%	
Time Delay		1.27 [4.17]	27 [4.17] ns/ft [ns		
Shielding Effectiveness	90			dB	
DWV (DC)			1,000	Vdc	
Jacket Spark			3,000	Vrms	
nner Conductor DC Res <mark>ist.</mark>			7.6	Ohms/1000ft	
Outer Conductor DC Resist.			18.1	Ohms/1000ft	
Nominal Capacitance		25.4		pF/ft	
		[83.33]		[pF/m]	
Nominal Inductance		0.064		uH/ft	
		[0.21]		[uH/m]	
Input Power (Peak)			2.5	kWatts	

#### **Performance by Frequency Band**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.05	0.15	0.45	0.9	1.5	GHz
Attenuation, Typ	2.5 8.2	4.4 14.44	7.8 25.59	11.1 36.42	14.5 47.57	dB/100ft dB/100m

LMR-LW195-BULK DATA SHEET



# **Configuration:**

Low Loss, Outdoor Flexible Cable
2 Shield(s)

## **Features:**

- Max Operating Frequency of 8 GHz
- Phase Velocity 80% VoP
- Aluminum Shielding Resulting in a Light Weight Coax
- Max Operating Temperature +85°C
- PE Jacket
- Min Install Bend Radius of 0.5 inches

## **Applications:**

- General Purpose RF Interconnect
- Laboratory Applications
- Antenna Installs
- RF Test Systems
- Wireless Communications

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com Fairview Microwave

an INFINIT<sup>®</sup> brand

Power In (CW), Max	680	390	220	160	120	Watts
Description	F6	F7	F8	F9	F10	Units
Frequency	1.8	2	2.5	5.8	8	GHz
Attenuation, Typ	16 52.49	16.9 55.45	19 62.34	29.9 98.1	35.7 117.13	dB/100ft dB/100m
Power In (CW), Max	110	100	90	60	40	Watts

### **Mechanical Specifications**

Diameter Weight		).195 in [4.95 mm] ).016 lbs/ft [0.02 kg/m]
Min. Bend Radius (Insta Min. Bend Radius (Repe Bending Moment Tensile Strength Flat Plate Crush	eated) 2 0	0.5 in [12.7 mm] 2 in [50.8 mm] 0.2 lbs-ft [0.27 N-m] 40 lbs [18.14 kg] 15 lbs/in [0.27 kg/mm]

#### **Construction Specifications**

Description	Material and Plating	Diameter
Inner Conductor	Copper, 1 Strands	0.037 in [0.94 mm]
Conductor Type	Solid	
Dielectric	Foam PE	0.11 in [2.79 mm]
First Shield	Aluminum Tape	[]
Second Shield	Aluminium	[]
Jacket	PE, Black	0.195 in [4.95 mm]

#### **Environmental Specifications**

Temperature	
Operating Range	-40 to +85 deg C
Installation Range	-40 to +85 deg C
Storage Range	-70 to +85 deg C

## Compliance Certifications (see product page for current document)

### **Plotted and Other Data**

Notes:

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

LMR-LW195-BULK DATA SHEET






Times Microwave LMR-LW195 Low Loss Flexible Coax Cable Black PE Jacket Light Weight from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: Times Microwave LMR-LW195 Low Loss Flexible Coax Cable Black PE Jacket Light Weight LMR-LW195-BULK

URL: https://www.fairviewmicrowave.com/Imr-Iw195-low-loss-flexible-coax-cable-pe-jacket-Imr-Iw195-bulk-p.aspx



an INFINIT® brand





301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689