



BNC Male Connector Crimp/Solder Attachment for LMR-400 Cable

Times Microwave Systems Connector Specification

BNC male connector with crimp/solder attachment for LMR-400, part number TC-400-BM-X, from Fairview Microwave is in-stock and ships same day. This BNC male connector operates up to a maximum frequency of 6 GHz and offers good VSWR of 1.3:1.

Fairview's BNC male connector TC-400-BM-X datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.3:1	
Insertion Loss			0.25	dB
DWV (AC)			1,500	Vrms
Insulation Resistance	5,000			MOhms

Mechanical Specifications

Size

 Length
 1.91 in [48.51 mm]

 Width/Dia.
 0.55 in [13.97 mm]

 Weight
 0.083 lbs [37.65 g]

 Mating Cycles
 500 Cycles

Material Specifications

Description	Material	Plating Gold 50 microns	
Contact	Brass		
Insulation	PTFE		
Body	Brass	Tri-Metal 80 microns	
Coupling Nut	Brass	Tri-Metal 80 microns	
Gasket	Silicone		
Crimp Sleeve	Brass	Tri-Metal 80 microns	



Configuration:

- BNC Male Connector
- 50 Ohms
- Straight Body Geometry
- LMR-400 Interface Type
- Crimp/Solder Attachment

Features:

- Operating Frequency of 6 GHz Max.
- Good VSWR of 1.3:1
- · Gold Plated Brass Contact
- 50 microns contact plating

Applications:

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Environmental Specifications

Temperature

Operating Range Shock Vibration Thermal Shock -55 to +125 deg C MIL-STD 202G, Meth.213, Cond G MIL-STD 202G, Meth.204, Cond B MIL-STD 202G, Meth.107, Cond B

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

BNC Male Connector Crimp/Solder Attachment for LMR-400 Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: BNC Male Connector Crimp/Solder Attachment for LMR-400 Cable TC-400-BM-X

URL: https://www.fairviewmicrowave.com/bnc-male-Imr-400-connector-tc-400-bm-x-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2019

REV 1.2 Page 2 of 3





