

SMA BIAS T 0.5 GHZ - 10 GHZ 200 MA PIN

SB5785

SPECIFICATIONS

ELECTRICAL

FREQUENCY: 0.5 GHZ- 10 GHZ
 IMPEDANCE: 50 OHMS
 VSWR: 1.60:1 MAX
 INSERTION LOSS: 2.0 DB MAX
 ISOLATION: 40 DB MIN
 VOLTAGE: 50 VDC MAX
 CURRENT: 700 MA MAX
 MAXIMUM RF POWER HANDLING: 5 WATTS



MECHANICAL

MATERIAL CONNECTORS: PASSIVATED STAINLESS STEEL
 MATERIAL CONTACTS: Au PLATED BeCu MIL-G-4520A
 INTERACE: MIL-STD-553

TEMPERATURE RANGE: -40° to 110°C

ROHS COMPLIANT

MEASUREMENTS BELOW ARE TYPICAL



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA BIAS T 0.5 GHZ - 10 GHZ 200 MA PIN

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SB5785	--
SCALE	SHEET		

ALL DIMENSIONS IN inches(MM) Typical