

SMA BIAS T 100 KHZ - 12400 MHZ 700 MA PIN

SB5792

SPECIFICATIONS

ELECTRICAL



FREQUENCY: 100 KHZ - 12400 MHZ
 IMPEDANCE: 50 OHMS
 VSWR: 1.60:1 MAX
 INSERTION LOSS: 2.0 DB MAX
 ISOLATION: 40 DB MIN
 VOLTAGE: 50 VDC MAX
 CURRENT: 700 MA MAX
 MAXIMUM RF POWER HANDLING: 5 WATTS

MECHANICAL

MATERIAL CONNECTORS: PASSIVATED STAINLESS STEEL
 MATERIAL CONTACTS: Au PLATED BeCu MIL-D-4520A
 INTERFACE: MIL-STD-883

TEMPERATURE RANGE: -55° to 120°C
 ROHS COMPLIANT

MEASUREMENTS BELOW ARE TYPICAL



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA BIAS T 100 KHZ - 12400 MHZ 700 MA PIN

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SB5792	A
SCALE	SHEET		

ALL DIMENSIONS IN inches(MM) Typical