

TNC-M RG55, RG58 GRIP ASSY RA

SC4266

SPECIFICATIONS

ELECTRICAL:



FREQUENCY: 0-6 GHZ
VSWR 1.3:1 MAX
IMPEDANCE: 50 OHMS

MECHANICAL:

MATERIAL BODY: NICKLE PLATED BRASS
CENTER CONTACT: BRASS
CONTACT PLATING: Si QQ-S-365
INSULATOR: TEFLON
CAPTIVATED CONTACT
INTERFACE: MIL-STD-348B
ROHS COMPLIANT
OP. TEMP RANGE: -55°C- +155°C

ASSEMBLY INSTRUCTIONS:

SLIDE BACKNUT ONTO CABLE
TRIM CABLE AS SHOWN
SLIT CABLE, 2 PLACES AS SHOWN, 180° APART
SLIDE PIN ASSEMBLY UNDER BRAID
SOLDER PIN ASSEMBLY TO CENTER CONDUCTOR
INSERT ASSEMBLY INTO BODY
TIGHTEN BY HOLDING NUT, TURNING BODY



STRIPPING DIMENSIONS

FAIRVIEW MICROWAVE INC.				
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM				
TITLE				
TNC-M RG55, RG58 GRIP ASSY RA				
SIZE	CAGE CODE	DWG NO	REV	
A	3FKR5	SC4266	--	
SCALE			SHEET	