

# BNC-F RG316 RG174 GRIP

SC6013

## SPECIFICATIONS

### ELECTRICAL:


FREQUENCY: 0-11 GHZ  
 VSWR 1.3:1 MAX  
 IMPEDANCE: 50 OHMS

### MECHANICAL:


MATERIAL BODY: NICKLE PLATED BRASS  
 CENTER CONTACT: BeCu  
 CONTACT PLATING: Si QQ-S-365  
 CAPTIVATED CONTACT  
 INSULATOR: TEFLON  
 INTERFACE: MIL-STD-348B  
 ROHS COMPLIANT  
 OP. TEMP RANGE: -55°C- +155°C

### ASSEMBLY INSTRUCTIONS:

SLIDE BACKNUT ONTO CABLE  
 TRIM CABLE AS SHOWN  
 SLIT CABLE, 2 PLACES AS SHOWN, 180° APART  
 SLIDE PIN ASSEMBLY UNDER BRAID  
 SOLDER PIN ASSEMBLY TO CENTER CONDUCTOR  
 INSERT ASSEMBLY INTO BODY  
 TIGHTEN BY HOLDING NUT, TURNING BODY



1.06"



STRIPPING DIMENSIONS

**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

**BNC-F RG316 RG174 GRIP**

SIZE	CAGE CODE	DWG NO	REV
<b>A</b>	<b>3FKR5</b>	<b>SC6013</b>	
SCALE	SHEET		