




SPECIFICATIONS


ELECTRICAL:

FREQUENCY: 0-11 GHZ
 VSWR 1.3:1 MAX @ 9 GHZ
 IMPEDANCE: 50 OHMS

MECHANICAL:

MATERIAL BODY: NICKLE PLATED BRASS
 CENTER CONTACT: BRASS
 CONTACT PLATING: Au
 INSULATOR: TEFLON
 ROHS COMPLIANT
 OP. TEMP RANGE: -55°C- +155°C

STRIPPING DIMENSIONS



S. M. ELECTRONICS L.L.C.
 FAIRVIEW, TX 75069 WWW.SMELECTRONICS.US

TITLE

N-M CRIMP RG174, RG316

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SC9120	--
SCALE	SHEET		