

N-M .141" SEMIRIGID CLAMP

SC9194

SPECIFICATIONS

ELECTRICAL:


FREQUENCY: 0-12 GHZ
 VSWR 1.3:1 MAX
 IMPEDANCE: 50 OHMS

MECHANICAL:

MATERIAL BODY: NICKLE PLATED BRASS
 CENTER CONTACT: BRASS
 CONTACT PLATING: Si QQ-S-350
 INSULATOR: TEFLON
 INTERFACE: MIL-STD-348B
 ROHS COMPLIANT
 OP. TEMP RANGE: -55°C- +155°C

ASSEMBLY INSTRUCTIONS:

TRIM CABLE AS SHOWN;
 SLIDE BACKNUT, WASHER, GASKET, CLAMP ON CABLE;
 SOLDER FERRULE TO JACKET;
 SOLDER CONTACT TO CENTER CONDUCTOR
 INSERT CABLE ASSEMBLY INTO JACKET & TIGHTEN BACKNUT



STRIPPING DIMENSIONS

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

N-M .141" SEMIRIGID CLAMP

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SC9194	--
SCALE	SHEET		