

N-M .141" SEMIRIGID TRIM & SOLDER

SC9196

SPECIFICATIONS

ELECTRICAL:


FREQUENCY: 0-12 GHZ
VSWR 1.3:1 MAX
IMPEDANCE: 50 OHMS

MECHANICAL:

MATERIAL BODY: Si PLATED BRASS
CENTER CONTACT: BRASS
CONTACT PLATING: Au MIL-G-45204
CAPTIVATED CONTACT
INSULATOR: TEFLON
INTERFACE: MIL-STD-348B
ROHS COMPLIANT
OP. TEMP RANGE: -55°C- +155°C

ASSEMBLY INSTRUCTIONS:

TRIM CABLE AS SHOWN;
INSERT CABLE INTO BODY, KEEPING END
OF CABLE FLUSH WITH DIELECTRIC;
SOLDER CABLE JACKET TO BODY



STRIPPING DIMENSIONS

	FAIRVIEW MICROWAVE INC.				
	ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM				
	TITLE				
	N-M .141" SEMIRIGID TRIM & SOLDER				
	SIZE	CAGE CODE	DWG NO		REV
	A	3FKR5	SC9196		--
	SCALE			SHEET	