

RA QMA Male Low PIM Connector Solder Attachment for TFT-5G-402

TC-402-QM-RA-LP



Times Microwave Systems Connector Specification

Configuration

- QMA Male Connector
- 50 Ohms
- Right Angle Body Geometry
- Connector Interface Types: TFT-5G-402
- Low PIM Design

Features

- Operating Frequency of 3 GHz Max.
- Excellent VSWR of 1.2:1
- PIM levels better than -150 dBc
- Silver Plated Beryllium Copper Contact
- 200 µin contact plating

Applications

- General Purpose Test
- Wireless Communications
- Custom Cable Assemblies
- Low PIM Applications
- Distributed Antenna Systems (DAS)

Description

RA QMA Male Low PIM Connector Solder/Solder Attachment for TFT-5G-402 Cable, part number TC-402-QM-RA-LP, from Fairview Microwave is in-stock and ships same day. This QMA male connector operates up to a maximum frequency of 3 GHz and offers excellent VSWR of 1.2:1. The QMA male connector also has low passive intermodulation (PIM) of -150 dBc. Its right angle body geometry facilitates connections in tight spaces.

Fairview's RA QMA male connector TC-402-QM-RA-LP datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.2:1	
Insertion Loss			0.173	dB
Passive Intermodulation			-150	dBc
Operating Voltage (DC)			1,000	Vdc
Insulation Resistance	5,000			MOhms
Impedance		50		Ohms

Electrical Specification Notes:
Insertion Loss is $0.1 \cdot \sqrt{f(\text{GHz})}$

Mechanical Specifications

Size

Length	0.75 in [19.05 mm]
Width	0.413 in [10.49 mm]

RA QMA Male Low PIM Connector Solder Attachment for TFT-5G-402

TC-402-QM-RA-LP



Height	0.413 in [10.49 mm]
Weight	0.03 lbs [13.61 g]
Mating Cycles	100 Cycles
Cable Retention Force	33 lbs [14.97 kg]

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Silver 200 µin
Insulation	PTFE	
Body	Brass	Tri-Metal 80 µin
Coupling Nut	Brass	Tri-Metal 80 µin

Environmental Specifications

Temperature	
Operating Range	-40 to +85 deg C
Shock	MIL-STD 202G, Meth. 213, Cond. I
Vibration	MIL-STD 202G, Meth. 204, Cond. D
Thermal Shock	MIL-STD 202G, Meth. 107, Cond. B
Environmental Specification Notes:	
Climatic Class: IEC 60068 40/85/21	

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

RA QMA Male Low PIM Connector Solder Attachment for TFT-5G-402 from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [RA QMA Male Low PIM Connector Solder Attachment for TFT-5G-402 TC-402-QM-RA-LP](#)

URL: <https://www.fairviewmicrowave.com/qma-male-tft-402-connector-tc-402-qm-ra-lp-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

TC-402-QM-RA-LP CAD Drawing
RA QMA Male Low PIM Connector Solder Attachment for TFT-5G-402

